

CP3653-000 | OCC1P-11600-S2SESEB



OCC1P Wideband Splitter, planar, singlemode, 1x16, symmetrical split ratio, SC/APC, 0.9 mm cable, medium duty housing

OBSOLETE

This product was discontinued on: July 25, 2023

Replaced By:

SP-11600S2S2CBAA Wideband PLC Splitter, singlemode, 1x16, symmetrical split ratio, 0.900 mm
PLC 1X16 900UM IN/OUT SC/APC GRADE C cable, SLC/APC grade C

Product Classification

| | |
|------------------------------|--------------------------------------|
| Regional Availability | EMEA Latin America North America |
| Product Type | Splitter component |
| Product Series | OCC1P |

General Specifications

| | |
|---------------------------|--------------------------------|
| Device Type | Component, rectangular |
| Functionality | Splitting |
| Technology Type | Planar lightwave circuit (PLC) |
| Application | For use in FOSC closures |
| Circuits, quantity | 1 |
| Distribution Type | 1 x 16 splitter |
| Interface, Input | SC/APC |
| Interface, Output | SC/APC |
| Split Ratio | Symmetrical |
| Splitter, quantity | 1 |

Dimensions

| | |
|---------------------------------|-------------------|
| Pigtail Length, Input | 1.5 m 4.921 ft |
| Pigtail Length, Output | 1.5 m 4.921 ft |
| Pigtail Diameter, Input | 0.9 mm 0.035 in |
| Pigtail Diameter, Output | 0.9 mm 0.035 in |

Environmental Specifications

Qualification Standards Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

