

A7818470 | Optical Demultiplexer, 4 channels



CWDM Fiber Optical Module, Demux, 1470-1530 nm, LC/PC, 4 channels

- Trade Agreements Act (TAA) compliant

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	LGX

General Specifications

Device Type	Plug-in module
Functionality	Demultiplexing
Application	For use with LGX panels
Circuits, quantity	1
Distribution Type	4-channel CWDM
Interface, Input	LC/PC
Interface, Output	LC/PC
Multiplexers, quantity	1

Dimensions

Height	29 mm 1.142 in
Width	130 mm 5.118 in
Depth	185 mm 7.283 in

Optical Specifications

Channel Spacing	20 nm
------------------------	-------

Environmental Specifications

Operating Temperature	-5 °C to +70 °C (+23 °F to +158 °F)
------------------------------	-------------------------------------

Packaging and Weights

Height, packed	65 mm 2.559 in
-----------------------	------------------

A7818470 | Optical Demultiplexer, 4 channels

Width, packed	275 mm 10.827 in
Depth, packed	160 mm 6.299 in
Packaging quantity	1
Packaging Type	Box
Weight, gross	0.5 kg 1.102 lb
Weight, net	0.4 kg 0.882 lb