

# A7818472 | Optical Demultiplexer, 4 channels



CWDM Fiber Optical Module, Demux, 1550-1610 nm, LC/PC, 4 channels

- Trade Agreements Act (TAA) compliant

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	CWDM module
<b>Product Series</b>	LGX

## General Specifications

<b>Device Type</b>	Plug-in module
<b>Functionality</b>	Demultiplexing

## Dimensions

<b>Height</b>	29 mm   1.142 in
<b>Width</b>	130 mm   5.118 in
<b>Depth</b>	185 mm   7.283 in

## Packaging and Weights

<b>Height, packed</b>	65 mm   2.559 in
<b>Width, packed</b>	275 mm   10.827 in
<b>Depth, packed</b>	160 mm   6.299 in
<b>Weight, gross</b>	0.5 kg   1.102 lb
<b>Weight, net</b>	0.4 kg   0.882 lb