

A7818477 | Optical Multiplexer, 18 channels



CWDM Fiber Optical Module, Mux, 1270-1610 nm, LC/PC, 18 channels

- Trade Agreements Act (TAA) compliant

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	LGX

General Specifications

Functionality	Multiplexing
Application	For use with any 19" rack mount panels
Circuits, quantity	1
Distribution Type	18-channel CWDM
Interface, Input	LC/PC
Interface, Output	LC/PC
Multiplexers, quantity	1

Dimensions

Height	44 mm 1.732 in
Width	483 mm 19.016 in
Depth	290 mm 11.417 in

Optical Specifications

Channel Spacing	20 nm
------------------------	-------

Environmental Specifications

Operating Temperature	-5 °C to +70 °C (+23 °F to +158 °F)
------------------------------	-------------------------------------

Packaging and Weights

Height, packed	90 mm 3.543 in
Width, packed	548 mm 21.575 in

A7818477 | Optical Multiplexer, 18 channels

Depth, packed	345 mm 13.583 in
Packaging quantity	1
Packaging Type	Carton
Weight, gross	2.1 kg 4.63 lb
Weight, net	1.7 kg 3.748 lb