

760027433 | PNL-BK-024-SFA-LC02-BL-SHUTTERED

Adapter Pack, Black, 1000-Type, with 12 TeraSPEED® Singlemode duplex LC Adapters, blue, shuttered



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter pack
Product Brand	TeraSPEED®
Product Series	1000-style

General Specifications

Application	Used in conjunction with panels and enclosures (rack, wall, and floor mount) that accept 1000 style panels
Adapter Color	Blue
Adapter Cutout, quantity	24
Adapters, quantity	12
Body Style	Duplex
Color, front	Black
Interface	LC/UPC
Shuttered	Yes
Total Ports, quantity	12

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

760027433 | PNL-BK-024-SFA-LC02-BL-SHUTTERED

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted



Included Products

760056028 – TeraSPEED® LC Duplex Low Profile Shuttered Adapter, Blue, Single Pack
SFA-LC02-BL/LP-SHUTTERED

760056028 | SFA-LC02-BL/LP-SHUTTERED

TeraSPEED® LC Duplex Low Profile Shuttered Adapter, Blue, Single Pack



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	TeraSPEED®
Product Series	SFA

General Specifications

Body Style	Duplex
Color	Blue
Interface	LC/UPC
Interface Feature	Reduced footprint
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	2
Transmission Standards	TIA/EIA-568-B.3 TIA/EIA-604 FOCIS-3

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

