



Preferred ordering guide for NETCONNECT[®]

Asia-Pacific Ordering Guide

Q4 2023

COMMScope[®]

Table of contents

NETCONNECT® Installer Partner	5
Benefits of being a CommScope NETCONNECT® Installer Partner	6
Requirements of a CommScope NETCONNECT® Installer Partner	6
Warranties.....	7
Anti-Counterfeiting.....	8
Copper Solutions	9
Category 6A F/UTP	9
NETCONNECT® Category 6A F/UTP Cables	9
CommScope SL Discrete Distribution Module (DDM) Patch Panels, Unloaded	9
NETCONNECT® Category 6A S/FTP, High-density Solution	10
NETCONNECT® SLX Series Information Outlet without Dust Cover	10
NETCONNECT® SLX Series Information Outlet with Dust Cover.....	11
NETCONNECT® Eco-friendly Shielded Information Outlets	11
Color Caps.....	11
NETCONNECT® Angled Faceplates.....	12
NETCONNECT® Category 6A S/FTP Patch Cords.....	12
NETCONNECT® Category 6A S/FTP, High-density Solution.....	12
Category 6A U/UTP	13
Category 6A U/UTP Cables.....	13
CommScope Dynamic Angled Distribution Module Panels, Category 6A UTP	13
CommScope Distribution Module (DM) Patch Panels, Category 6A UTP.....	14
NETCONNECT® SL Series Information Outlet, without Dust Cover.....	14
CommScope Ceiling Connector Assembly (CCA) Solution	14
NETCONNECT® Category 6A U/UTP Patch cords	15
NETCONNECT® Category 6A U/UTP, High-density Solution	15
Category 6 U/UTP	16
NETCONNECT® Category 6 U/UTP Cables.....	16
CommScope Dynamic Angled Distribution Module Panels, Category 6 UTP.....	16
CommScope SL Discrete Distribution Module (DDM) Patch Panels, Unloaded	16
CommScope SL Discrete Distribution Module (DDM) Patch Panel, Loaded	16
NETCONNECT® SL Series Information Outlet, without Dust Cover.....	17
NETCONNECT® SL Series Information Outlet, with Dust Cover.....	17
NETCONNECT® SL Series Information Outlet, Packaged with a Clipsal Bezel, fit to Clipsal/ Schneider Faceplates	18
NETCONNECT® KJ Series Information Outlet, without Dust Cover, to use with Keystone Faceplates of Other Suppliers.....	18
NETCONNECT® Category 6 U/UTP, High Density Solution.....	18
NETCONNECT® Category 6 U/UTP Patch Cords.....	19
Category 6 F/UTP	20
NETCONNECT® Category 6 F/UTP Cables.....	20
CommScope SL Discrete Distribution Module (DDM) Patch Panels, Unloaded	20
NETCONNECT® Category 6 FTP, High-density Solutions	20
NETCONNECT® SLX Series Information Outlet with Dust Cover	21

Table of contents

NETCONNECT SLX Series Information Outlet without Dust Cover	21
NETCONNECT Category 6 F/UTP Patch Cords	21
Telephone – ADSL Systems	22
LSA-PLUS® Disconnect Module	22
LSA-PLUS® Distribution Rack & Backmount Frame (unloaded)	22
LSA-PLUS® Wall Boxes (unloaded)	22
ComProtect® Overvoltage Protection	23
LSA-PLUS® Insertion Tool with Sensor	23
Modular RJ45 Plug & Termination Tools	24
NETCONNECT® Category 6A RJ45 Modular Plug & Tool	24
NETCONNECT® Category 6 RJ45 Modular Plug & Tool	24
NETCONNECT® Modular Boot	25
NETCONNECT® Modular Plug Color Clip (Used with NPC Patch Cords)	25
Faceplate & Accessories	26
NETCONNECT® Faceplate US Style	26
NETCONNECT® Faceplate UK Style	26
NETCONNECT® Single and Dual Outlets 45 x 45 mm (“Mosaic”), used with Legrand Faceplate	26
NETCONNECT® Boxes	27
NETCONNECT® Consolidation Point	28
NETCONNECT® SL Tool	28
Horizontal Cable Management	29
Outdoor Application	30
NETCONNECT® Category 6	30
NETCONNECT® Category 6A F/UTP	30
Powered Fiber Solutions	31
1 and 2 Port PoE Extenders	32
Power Extenders/Fiber Pass-Thru	32
Power Supplies	32
Surface Mount Boxes	33
Plenum Powered Fiber Cable Transition Box	33
FiberGuide	34
Fiber Solutions	36
Fiber Optic Cable	36
CommScope Indoor, LSZH & OFNR Dual Rate Cable - APAC	36
CommScope Indoor, OFNP Distribution Cable - APAC	36
CommScope Indoor/Outdoor Gel LSZH Central Tube Cable - APAC	37
CommScope Indoor/Outdoor Gel LSZH Stranded Loose Tube Cable - APAC	37
CommScope Indoor/Outdoor Gel LSZH Central Loose Tube Cable, Armored - APAC	37
CommScope Indoor/Outdoor Gel LSZH Stranded Loose Cable, Armored - APAC	37
CommScope Indoor/Outdoor LSZH Distribution Cable - APAC	38
CommScope Indoor/Outdoor, Figure 8 Drop Cable - APAC	38
CommScope Outside Plant Gel Central Tube Cable - APAC	39

Table of contents

CommScope Outside Plant Gel Loose Tube Cable - APAC	39
CommScope Outside Plant Gel Central Tube Cable, Armored - APAC	39
CommScope Outside Plant Gel Loose Tube Cable, Armored - APAC	39
Fiber Panel Portfolios	40
Panel, Wall Boxes, and Accessories	40
G2 Modules	41
G2 Splice Cassettes	42
G2 Adapter Packs	43
Standard Density Fiber Solutions	44
LGX/1000 Style Panels and Wall Boxes	44
LGX/1000 Style Splicing Cassettes	44
APAC Local Splicing Solutions	45
1U 36F/72F Fiber Splicing Shelf	45
1U 12F/24F/48F/96F Fiber Splicing Shelf	45
FMS All-In-One Splicing Panel	46
Fiber Connectors and Adapters.....	47
QWIK II Connector Kits	47
APAC Local LC/SC Adapters	47
Qwik-Fuse Connector Kits, Tools and Accessories.....	48
Qwik-Fuse MPO Connector Kits	48
Method A MPO Trunk and Patch Cords.....	52
LL Fiber Optic Patch Cords.....	53
ULL Fiber Optic Patch Cords	53
Fiber Pigtails.....	54
APAC Local Fiber Patch Cords and Pigtails.....	55
CAF CommScope Armored Fiber Patch Cords	56
Rack and Cabinet.....	57
CommScope Open Rack - ASEAN.....	57
CommScope Wall Mount Rack.....	57
CommScope Rack Accessories - Shelves	58
CommScope Rack Accessories - Fans.....	58
CommScope Rack Accessories - AC Power Distribution Units	58

NETCONNECT® Installer Partner

NETCONNECT is a complete portfolio of standards-based, technologically superior solutions that support voice, data, security, audio, video, controls and other building and campus systems. The NETCONNECT Structured Cabling Solution provides a complete fiber and copper cable, connectivity and cable management solution from the entrance facility to the desktop and across the campus.

PartnerPRO® NETWORK

The PartnerPRO® Network
opportunity:
new business, more revenue

The PartnerPRO Network is designed to help our partners find new revenue opportunities in today's competitive, global marketplace. A partnership with CommScope gives you a unique opportunity to begin from a position of instant brand recognition and greater trust, especially with new customers. Our partnership enables you to be among the first to offer your customers the latest technologies and innovative solutions from CommScope that can improve network performance, capacity and cost.

CommScope is committed
to giving our Partners the best
tools and support to serve our
mutual customers


Members are provided access to the CommScope PartnerPRO Portal (CPP): technology created to simplify collaboration, increase knowledge sharing and streamline the warranty process



Next Steps

As the marketplace continues to become more crowded, differentiating yourself from the competition in a meaningful way becomes more difficult. Becoming a CommScope NETCONNECT Partner allows you to leverage the global equity of the CommScope brand and create greater value for your customers.

To learn more about the CommScope Partner programs available to you, contact your local CommScope representative or visit commscope.com.



Benefits of being a CommScope NETCONNECT® Installer Partner

Partners enjoy benefits that can help grow business, expand customer base and maximize profit margins.

- Provide customers maximum warranty protection on CommScope products
- Increased visibility via CommScope's online Partner Locator
- Access to discounted pricing on demonstration, testing and exhibition products
- North America: Access to available co-op marketing funds
- Participation in valuable incentive programs
- Use of the CommScope PartnerPRO Network logo and local sales support
- Access to CommScope design tools, resources and technical support teams
- Inclusion in regional partner conferences, events and Partner communication calls
- Access to regular technical meetings, training and updates from CommScope
- Ongoing education and training on CommScope solutions, including online instruction
- Business events opportunities at CommScope global executive briefing centers
- Eligible to provide extended warranty terms for CommScope authorized projects
- Dedicated Executive Sponsor



Requirements of a CommScope NETCONNECT® Installer Partner

- Complete and submit an online application via the CommScope PartnerPRO™ Portal (CPP)
- All CommScope products must be purchased through PartnerPRO Network distributors or authorized resellers
- Participate in quarterly business reviews with CommScope to review sales, leads and business development activities
- Complete the CommScope Annual Partnership Process
- Receive a minimum number of customer surveys per year and maintain an average survey score (2 surveys/4.0 average score)

Training Requirements

- | | |
|--|---------------|
| · Installing Premises Cabling Systems, ACT 1: SP3801 or ND3801 | 2 individuals |
| · Certifying and Troubleshooting Premises Cabling Systems, ACT 2: SP3802 or ND3802 | 2 individuals |
| · Designing Premises Cabling Systems, ACT 3: SP3000 or ND3803 or SP3321 | 1 individual |

Warranties

CommScope guarantees that all NETCONNECT solutions will deliver on the terms and conditions of our 25-year assurance warranty:

- Will meet—and exceed—published specifications
- Will support all warranted, specified applications
- Will be replaced at no cost, whether a problem arises in the first year or the 25th

It's all covered under the CommScope Network Infrastructure System 25 Year Extended Product Warranty and Application Assurance.

Only the best solution on the market can afford to offer this degree of warranty protection.

Full details at commscope.com/resources/warranties


CommScope warrants, for a period of twenty-five (25) years from the Certification Date, that Products in the Registered System shall be free from defects in materials or workmanship subject, to the terms and conditions and limitations of CommScope's Limited Product Warranty in effect at the date of sale.



CommScope Limited Product Warranty



CommScope Network Infrastructure System 25 Year Extended Product and Application Warranty



CommScope Product and Software Warranty Handbook

CommScope structured cabling solutions are backed by our industry-leading 25-year Extended Product Warranty and Application Assurance

Don't accept less than CommScope's best.

Validate your solutions to verify genuine CommScope quality! Counterfeit products are a problem—but they don't have to be YOUR problem. CommScope is a trusted global provider of high-performance network infrastructure solutions. Counterfeiters try to exploit our reputation by illegally selling counterfeit products that do not deliver the same performance or reliability.

Protect your network by verifying you're using genuine CommScope solutions.

The risks of using counterfeit solutions go far beyond simply reduced performance. For example, counterfeiters are known to use cheap alloy or aluminum instead of copper, which can seriously degrade network performance. They can also use materials in jackets and connectors that don't meet CMP (communication multipurpose cable, plenum), CMR (communication multipurpose cable, riser), CM (horizontal cable) and LSZH (low smoke zero halogen) flammability requirements. This not only puts safety and property at risk—knowingly using noncompliant counterfeit solutions could violate building codes or be considered negligence or fraud.

CommScope has zero tolerance for counterfeiters.

To ensure every customer gets nothing but CommScope's best performance and quality, we make it easy for you to check the authenticity of your CommScope solutions.

Scan and be certain.

Each package features a security hologram and scannable QR code that can verify the authenticity of your product in seconds. Just scan the QR code with the "CheckifReal" App from any smart device for instant confirmation.



Use your smartphone to scan the QR code with the "CheckifReal" app from any smart device.



Copper solutions

Category 6A F/UTP



NETCONNECT CATEGORY 6A F/UTP CABLES

MATERIAL ID	DESCRIPTION	RATE	COLOR
884024508/10	NETCONNECT CS44Z1, Category 6A Cable, 4 pair, 23 AWG, F/UTP, LSZH, 305M, Reel, White	LSZH	White
884028508/10	NETCONNECT CS44Z1, Category 6A Cable, 4 pair, 23 AWG, F/UTP, LSZH, 305M, Reel, Blue	LSZH	Blue
884020108/10	NETCONNECT CS44CM, Category 6A Cable, 4 pair, 23 AWG, F/UTP, LSZH, 305M, Reel, Blue	CM	White



COMMScope SL DISCRETE DISTRIBUTION MODULE (DDM) PATCH PANELS, UNLOADED

MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	SPACE	PORT	TYPE
760237046	CPP-SDDM-SL-1U-24	CommScope SL DDM Patch Panel, STP, 1U, 24 port, Straight	1U	24	Straight
760237047	CPP-SDDM-SL-2U-48	CommScope SL DDM Patch Panel, STP, 2U, 48 port Straight	2U	48	Straight
760237048	CPPA-SDDM-SL-1U-24	CommScope SL DDM Patch Panel, STP, 1U, 24 port, Angled	1U	24	Angled
760237049	CPPA-SDDM-SL-2U-48	CommScope SL DDM Patch Panel, STP, 2U, 48 port Angled	2U	48	Angled
760237050	CPPR-SDDM-SL-1U-24	CommScope SL DDM Patch Panel, STP, 1U, 24 port, Recessed Angled	1U	24	Recessed Angled
760237051	CPPR-SDDM-SL-2U-48	CommScope SL DDM Patch Panel, STP, 2U, 48 port, Recessed Angled	2U	48	Recessed Angled

Copper solutions

Category 6A F/UTP



NETCONNECT CATEGORY 6A S/FTP, HIGH-DENSITY SOLUTION			
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	SOLUTION TYPE
760237066	CPP-6A-SDDM-SL-1U-48	CommScope SL DDM Panel, STP, 1U, 48 port, Straight 1U	Mix Media option
760253767	CPP-1HU-E-HD	CommScope Patch Panel, Empty, 1U	Mix Media option
760238659	CPP-FMAE-KIT-4PK	Module Adapter (4 pcs) for Fiber Adapters, Black	Mix Media option
760243427	CPP-FMAE-KIT-4PK BLK		Mix Media option
760242925	CPP-SDDM-SLHD-KIT-4PK	CommScope Shielded DDM for HDSL Jacks Black (4 pcs) incl ground kit and 48 jacks SLX Cat6A jack.	Mix Media option



NETCONNECT SLX SERIES INFORMATION OUTLET WITHOUT DUST COVER		
MATERIAL ID	DESCRIPTION	COLOR*
2153449-1	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, without Dust Cover, Almond	Almond
2153449-2	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, without Dust Cover, Black	Black
2153449-4	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, without Dust Cover, Silver Gray	Silver Gray
2153449-5	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, without Dust Cover, Orange	Orange
2153449-6	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, without Dust Cover, Blue	Blue
2153449-7	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, without Dust Cover, Red	Red
2153449-8	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, without Dust Cover, Yellow	Yellow
2153449-9	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, without Dust Cover, Green	Green
1-2153449-3	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, without Dust Cover, Alpine white	White

Copper solutions

Category 6A F/UTP



NETCONNECT SLX SERIES INFORMATION OUTLET WITH DUST COVER

MATERIAL ID	DESCRIPTION	COLOR*
2153365-1	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, with Dust Cover, Almond	Almond
2153365-2	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, with Dust Cover, Black	Black
2153365-4	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, with Dust Cover, Gray	Gray
2153365-5	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, with Dust Cover, Orange	Orange
2153365-6	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, with Dust Cover, Blue	Blue
2153365-7	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, with Dust Cover, Red	Red
2153365-8	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, with Dust Cover, Yellow	Yellow
2153365-9	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, with Dust Cover, Green	Green
1-2153365-3	NETCONNECT SLX Information Outlet, Category 6A, S/FTP, with Dust Cover, White	White



ECO-FRIENDLY SHIELDED INFORMATION OUTLETS

MATERIAL ID	DESCRIPTION	COLOR
4-2153449-2	AMP-TWIST SLX Series Modular Jack, category 6A, shielded , 4 Pair, without dust cover, black (24 ea/pkg)	Black
4-2153449-4	AMP-TWIST SLX Series Modular Jack, category 6A, shielded , 4 Pair, without dust cover, gray (24 ea/pkg)	Gray
5-2153449-3	AMP-TWIST SLX Series Modular Jack, category 6A, shielded , 4 Pair, without dust cover, alpine white (24 ea/pkg)	A. White

COLOR CAPS

MATERIAL ID	DESCRIPTION	COLORS
1-2848025-1	COLOR CAP W/DC,AT-SLX,ALD,50	Almond
1-2848025-2	COLOR CAP W/DC,AT-SLX,BLK,50	Black
1-2848025-3	COLOR CAP W/DC,AT-SLX,WHT,50	White
1-2848025-4	COLOR CAP W/DC,AT-SLX,GRY,50	Gray
1-2848025-5	COLOR CAP W/DC,AT-SLX,ORG,50	Orange
1-2848025-6	COLOR CAP W/DC,AT-SLX,BLU,50	Blue
1-2848025-7	COLOR CAP W/DC,AT-SLX,RED,50	Red
1-2848025-8	COLOR CAP W/DC,AT-SLX,YEL,50	Yellow
1-2848025-9	COLOR CAP W/DC,AT-SLX,GRN,50	Green
2-2848025-0	COLOR CAP W/DC,AT-SLX,VIO,50	Violet

Copper solutions

Category 6A F/UTP



NETCONNECT ANGLED FACEPLATE, RECOMMENDED TO USE WITH SLX INFORMATION OUTLETS			
MATERIAL ID	DESCRIPTION	PORT	COLOR
760245679	FP KIT, BS, 1 PORT, ANGLED SHUTTERED	1	White
760245680	FP KIT, BS, 2 PORT, ANGLED SHUTTERED	2	White



NETCONNECT CATEGORY 6A S/FTP PATCH CORDS			
MATERIAL ID	DESCRIPTION	RATE	COLOR
NPC6ASZDB-WT###M	NETCONNECT Patch cord, Category 6A, 4pair, Stranded S/FTP, LSZH, White, X m	LSZH	White
NPC6ASZDB-GY###M	NETCONNECT Patch cord, Category 6A, 4pair, Stranded S/FTP, LSZH, Grey, X m	LSZH	Grey
NPC6ASZDB-BL###M	NETCONNECT Patch cord, Category 6A, 4pair, Stranded S/FTP, LSZH, Blue, X m	LSZH	Blue
NPC6ASZDB-YL###M	NETCONNECT Patch cord, Category 6A, 4pair, Stranded S/FTP, LSZH, Yellow, X m	LSZH	Yellow
NPC6ASZDB-RD###M	NETCONNECT Patch cord, Category 6A, 4pair, Stranded S/FTP, LSZH, Red, X m	LSZH	Red
NPC6ASZDB-GN###M	NETCONNECT Patch cord, Category 6A, 4pair, Stranded S/FTP, LSZH, Green, X m	LSZH	Green
NPC6ASZDB-BK###M	NETCONNECT Patch cord, Category 6A, 4pair, Stranded S/FTP, LSZH, Black, X m	LSZH	Black
NCC44FZDB-08###M	NETCONNECT Patch cord, Category 6A, 4pair, Solid F/UTP, LSZH, White, X m	LSZH	White

NOTE: Replace ### with length in met. Eg: 001 = 1m, 002 = 2m, 003 = 3m, 005= 5m.
Stranded Cord supports length up to 30 meters. Solid Cord support length up to 100 meters




NETCONNECT CATEGORY 6A S/FTP, HIGH-DENSITY SOLUTION			
MATERIAL ID	DESCRIPTION	RATE/TYPE	COLOR
760237066	CPP-6A-SDDM-SL-1U-48: CommScope SL DDM Panel, STP, 1U, 48 port, Straight	1U, Straight	Black
760242924	CPP-1U-E-HD CommScope Patch Panel, Empty, 1U	1U, Straight	Black
760238659	CPP-FMA-KIT-4PK Module Adapter (4 pcs) for Fiber Adapters, Black		Black
760242925	CPP-SDDM-SLHD-KIT-4PK CommScope Shielded DDM for HDSL information outlets Black (4 pcs) incl ground kit and 48 information outlets SLX Category 6A information outlet		Black
1859916-X	NETCONNECT Patch cord, Category 6A, 4pair, 30AWG, S/FTP, LSZH, White, X m	LSZH	White
1859918-X	NETCONNECT Patch cord, Category 6A, 4pair, 30AWG, S/FTP, LSZH, Grey, X m	LSZH	Grey
1859919-X	NETCONNECT Patch cord, Category 6A, 4pair, 30AWG, S/FTP, LSZH, Red, X m	LSZH	Red

NOTE: Replace X with length in met. Eg: 1 = 1m, 2 = 2m, 3 = 3m, 5= 5m

Copper solutions

Category 6A U/UTP



CATEGORY 6A U/UTP CABLES

MATERIAL ID	DESCRIPTION	RATE	AW	COLOR	LENGTH	PACKAGING
884057804/10	CS41Z1 BLU C6A 4/23 U/UTP RL 305M	LSZH	23 AWG	Blue	305 m	Reel
884060904/10	CS41Z1 GRY C6A 4/23 U/UTP RL 305M	LSZH	23 AWG	Gray	305 m	Reel
884050804/10	CS41Z1 WHT C6A 4/23 U/UTP RL 305M	LSZH	23 AWG	White	305 m	Reel
884066604/10	CS41Z3 BLU C6A 4/23 U/UTP RL 305M	LSZH	23 AWG	Blue	305 m	Reel
884056904/10	CS41Z3 GRY C6A 4/23 U/UTP RL 305M	LSZH	23 AWG	Gray	305 m	Reel
884063304/10	CS41Z3 WHT C6A 4/23 U/UTP RL 305M	LSZH	23 AWG	White	305 m	Reel
884064004/10	CS41CM BLU C6A 4/23 U/UTP RL 305M	CM	23 AWG	Blue	305 m	Reel
884062904/10	CS41CM GRY C6A 4/23 U/UTP RL 305M	CM	23 AWG	Gray	305 m	Reel
884056804/10	CS41CM WHT C6A 4/23 U/UTP RL 305M	CM	23 AWG	White	305 m	Reel
884057904/10	CS41R BLU C6A 4/23 U/UTP RL 305M	CMR	23 AWG	Blue	305 m	Reel
884057204/10	CS41R GRY C6A 4/23 U/UTP RL 305M	CMR	23 AWG	Gray	305 m	Reel
884067804/10	CS41R WHT C6A 4/23 U/UTP RL 305M	CMR	23 AWG	White	305 m	Reel
460158784	Cat 6A F/UTP Cable, 23AWG. OD 7.9mm.	OUTDOOR	23 AWG	Black	305 m	Reel
884048304/10	CS41CM BLU C6A 4/24 U/UTP RL 305M	CM	24 AWG	Blue	305 m	Reel
884048904/10	CS41CM GRY C6A 4/24 U/UTP RL 305M	CM	24 AWG	Gray	305 m	Reel
884037504/10	CS41CM WHT C6A 4/24 U/UTP RL 305M	CM	24 AWG	White	305 m	Reel
884049104/10	CS41R BLU C6A 4/24 U/UTP RL 305M	CMR	24 AWG	Blue	305 m	Reel
884039004/10	CS41R GRY C6A 4/24 U/UTP RL 305M	CMR	24 AWG	Gray	305 m	Reel
884015004/10	CS41R WHT C6A 4/24 U/UTP RL 305M	CMR	24 AWG	White	305 m	Reel
884041004/10	CS41Z1 BLU C6A 4/24 U/UTP RL 305M	LSZH	24 AWG	Blue	305 m	Reel
884045804/10	CS41Z1 GRY C6A 4/24 U/UTP RL 305M	LSZH	24 AWG	Gray	305 m	Reel
884049604/10	CS41Z1 WHT C6A 4/24 U/UTP RL 305M	LSZH	24 AWG	White	305 m	Reel
884047004/10	CS41Z3 BLU C6A 4/24 U/UTP RL 305M	LSZH	24 AWG	Blue	305 m	Reel
884018004/10	CS41Z3 GRY C6A 4/24 U/UTP RL 305M	LSZH	24 AWG	Gray	305 m	Reel
884042604/10	CS41Z3 WHT C6A 4/24 U/UTP RL 305M	LSZH	24 AWG	White	305 m	Reel




COMMSCOPE DYNAMIC ANGLED DISTRIBUTION MODULE PANELS, CATEGORY 6A UTP

MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	SPACE	PORTS	TYPE
760244168	CPPD-6A-DM-1U-24	CommScope Dynamic Angled Distribution Module Panel, Cat6A, UTP, 1U, 24 port	1U	24	Dynamic Angle

Copper solutions

Category 6A U/UTP



COMMSCOPE DISTRIBUTION MODULE (DM) PATCH PANELS, CATEGORY 6A UTP

MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	SPACE	PORTS	TYPE
760237032	NPP-6A-DM-1U-24	CommScope SL DM Patch Panel, Cat6A, UTP, 1U, 24 port, Straight	1U	24	Straight
760237033	NPP-6A-DM-2U-48	CommScope SL DM Patch Panel, Cat6A, UTP, 2U, 48 port, Straight	2U	48	Straight
760237036	NPPR-6A-DM-1U-24	CommScope SL DM Patch Panel, Cat6A, UTP, 1U, 24 port, Recessed Angled	1U	24	Recessed Angled
760237037	NPPR-6A-DM-2U-48	CommScope SL DM Patch Panel, Cat6A, UTP, 2U, 48 port, Recessed Angled	2U	48	Recessed Angled



NETCONNECT SL SERIES INFORMATION OUTLET, WITHOUT DUST COVER

MATERIAL ID	DESCRIPTION	COLOR
760241184	SL10G, L.ALD	Almond
760241185	SL10G, BLK	Black
760241186	SL10G-GRAY	Gray
760241187	SL10G-ORANGE	Orange
760241188	SL10G-BLU	Blue
760241189	SL10G-RED	Red
760241190	SL10G-YELLOW	Yellow
760241191	SL10G-GREEN	Green
760241192	SL10G-VIOLET	Violet
760241193	SL10G-E.IVORY	Electric Ivory
760241194	SL10G-A.WHT	White

*Please contact us with questions about information outlets with dust cover



COMMSCOPE CEILING CONNECTOR ASSEMBLY SOLUTION

MATERIAL ID	DESCRIPTION	COLOR
760234921	CommScope Ceiling Connector Assembly (CCA) without cordage	White
760235590	CommScope Category 6A U/UTP Cord, LSZH, RJ45 to Ceiling connector, 1.5 ft., white	White
760235591	CommScope Category 6A U/UTP Cord, Plenum, RJ45 to Ceiling Connector, 1.5 ft., Black	Black
760235585	CommScope Category 6 U/UTP Cord, LSZH, RJ45 to Ceiling Connector, 1.5 ft., Black	Black
760235587	CommScope Category 6 U/UTP Cord, Plenum, RJ45 to Ceiling Connector, 1.5 ft., Black	Black
760235589	CommScope Category 6A U/UTP Cord, LSZH, RJ45 to Ceiling Connector, 1.5 ft., Black	Black

Copper solutions

Category 6A U/UTP



NETCONNECT CATEGORY 6A U/UTP PATCH CORDS			
MATERIAL ID	DESCRIPTION	RATE	COLOR
NPC6AUZDB-WT###M	NETCONNECT Patch cord, Category 6A, 4pair, Solid U/UTP, LSZH, White, X m	LSZH	White
NPC6AUZDB-GY###M	NETCONNECT Patch cord, Category 6A, 4pair, Solid U/UTP, LSZH, Gray, X m	LSZH	Gray
NPC6AUZDB-OR###M	NETCONNECT Patch cord, Category 6A, 4pair, Solid U/UTP, LSZH, Orange, X m	LSZH	Orange
NPC6AUZDB-BK###M	NETCONNECT Patch cord, Category 6A, 4pair, Solid U/UTP, LSZH, Black, X m	LSZH	Black
NPC6AUZDB-BL###M	NETCONNECT Patch cord, Category 6A, 4pair, Solid U/UTP, LSZH, Blue, X m	LSZH	Blue
NPC6AUZDB-GN###M	NETCONNECT Patch cord, Category 6A, 4pair, Solid U/UTP, LSZH, Green, X m	LSZH	Green
NPC6AUZDB-YL###M	NETCONNECT Patch cord, Category 6A, 4pair, Solid U/UTP, LSZH, Yellow, X m	LSZH	Yellow
NPC6AUZDB-RD###M	NETCONNECT Patch cord, Category 6A, 4pair, Solid U/UTP, LSZH, Red, X m	LSZH	Red
NCC44UZDB-08M###	NETCONNECT Patch cord, Category 6A, 4pair, Solid U/UTP, LSZH, White, X m	LSZH	White

NOTE: Replace ### with length in met. Eg: 001 = 1m, 002 = 2m, 003 = 3m, 005= 5m.
Stranded Cord supports length up to 30 meters. Solid Cord support length up to 100 meters



NETCONNECT CATEGORY 6A U/UTP, HIGH-DENSITY SOLUTION			
MATERIAL ID	DESCRIPTION	RATE	COLOR
CO199K2-02M###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, Blue, X m	CM-LS	Blue
CO199K2-08M###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, White, X m	CM-LS	Yellow
CO199K2-07M###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, Red, X m	CM-LS	Red
CO199K2-03M###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, Dark Gray, X m	CM-LS	Dark Gray
CO199K2-04M###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, Spring Green, X m	CM-LS	Spring Green
CO199K2-01M###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, Black, X m	CM-LS	Black
CO199K2-06M###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, Orange, X m	CM-LS	Orange
CO199K2-02M###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, Light Blue, X m	CM-LS	Light Blue
CO199K2-0LM###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, Violet, X m	CM-LS	Violet
CO199K2-09M###	CommScope Patch cord, Category 6A, 4pair, 28AWG, Stranded U/UTP, CM, Yellow, X m	CM-LS	Yellow

NOTE: Replace ### with length in met. Eg: 001 = 1m, 002 = 2m, 003 = 3m, 005= 5m

Copper solutions

Category 6 U/UTP



NETCONNECT CATEGORY 6 U/UTP CABLES				
MATERIAL ID	DESCRIPTION	JACKET	CONDUCTOR GAUGE	REGION
1427071-6	CS30CM WHT C6 4/24 U/UTP RIB 305M	CM	24 AWG	APAC
1427070-2	CS30Z1 WHT C6 4/24 U/UTP RIB 305M	LSZH	24 AWG	APAC
1967075-2	NETCONNECT Category 6 Cable, 4 pair, 24 AWG, U/UTP, PVC, 305m, Reel in box, Gray	PVC	24 AWG	India
884016994/10	CS31CM BLU C6 4/23 U/UTP RIB 305M	CM	23 AWG	APAC
884031194/10	CS31R GRY C6 4/23 U/UTP RIB 305M	CMR	23 AWG	APAC
884023394/10	CS31R BLU C6 4/23 U/UTP RIB 305M	CMR	23 AWG	APAC
884036494/10	CS31Z1 WHT C6 4/23 U/UTP RIB 305M	LSZH	23 AWG	APAC
884036214/10	CS37Z3 ORG C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	India
884036314/10	CS37Z3 GRY C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	India
884036614/10	CS37Z3 GRN C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	India
884036914/10	CS37Z3 WHT C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	India
884037014/10	CS37Z3 YEL C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	India
884037114/10	CS37Z3 RED C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	India
884037414/10	CS37Z3 BLU C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	India



COMMSCOPE DYNAMIC ANGLED DISTRIBUTION MODULE PANELS, CATEGORY 6 UTP				
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	SPACE	PORT
760244166	CPPD-6-DM-1U-24	CommScope Dynamic Angled Distribution Module Panel, Category 6, UTP, 1U, 24 port	1U	24



COMMSCOPE SL DISCRETE DISTRIBUTION MODULE (DDM) PATCH PANELS, UNLOADED				
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	SPACE	PORT
760237040	CPP-UDDM-SL-1U-24	CommScope SL DDM Patch Panel, UTP, 1U, 24 port, Straight	1U	24
760237041	CPP-UDDM-SL-2U-48	CommScope SL DDM Patch Panel, UTP, 2U, 48 port Straight	2U	48
760237042	CPPA-UDDM-SL-1U-24	CommScope SL DDM Patch Panel, UTP, 1U, 24 port, Angled	1U	24
760237043	CPPA-UDDM-SL-2U-48	CommScope SL DDM Patch Panel, UTP, 2U, 48 port Angled	2U	48
760237044	CPPR-UDDM-SL-1U-24	CommScope SL DDM Patch Panel, UTP, 1U, 24 port, Recessed Angled	1U	24
760237045	CPPR-UDDM-SL-2U-48	CommScope SL DDM Patch Panel, UTP, 2U, 48 port, Recessed Angled	2U	48

NOTE: Customer should order 9-1375055-2 (in bulk pack, PPQ= 24pcs) to have a fully loaded patch panel.

COMMSCOPE SL DISCRETE DISTRIBUTION MODULE (DDM) PATCH PANEL, LOADED				
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	SPACE	PORT
760242562	CPP-6-UDDM-SL-1U-24	CommScope SL DDM Patch Panel, UTP, 1U, 24 port, Straight	1U	24

Copper solutions

Category 6 U/UTP



NETCONNECT SL SERIES INFORMATION OUTLET, WITHOUT DUST COVER		
MATERIAL ID	DESCRIPTION	COLOR
1375055-1	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Almond	Almond
1375055-2	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Black	Black
1375055-4	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Gray	Gray
1375055-5	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Orange	Orange
1375055-6	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Blue	Blue
1375055-7	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Red	Red
1375055-8	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Yellow	Yellow
1375055-9	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Green	Green
1-1375055-3	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Alpine white	White
9-1375055-2	NETCONNECT SL Information Outlet, Category 6, UTP, without Dust Cover, Black, in bulk pack	Black



NETCONNECT SL SERIES INFORMATION OUTLET, WITH DUST COVER		
MATERIAL ID	DESCRIPTION	COLOR
1375187-1	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, Almond	Almond
1375187-2	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, Black	Black
1375187-4	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, Gray	Gray
1375187-5	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, Orange	Orange
1375187-6	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, Blue	Blue
1375187-7	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, Red	Red
1375187-8	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, Yellow	Yellow
1375187-9	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, Green	Green
1-1375187-0	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, Violet	Violet
1-1375187-3	NETCONNECT SL Information Outlet, Category 6, UTP, with Dust Cover, White	White

Copper solutions

Category 6 U/UTP



NETCONNECT SL SERIES INFORMATION OUTLET, PACKAGED WITH A CLIPSAL BEZEL, FIT TO CLIPSAL/SCHNEIDER FACEPLATES

MATERIAL ID	DESCRIPTION	COLOR
760238473	NETCONNECT SL Information Outlet with Clipsal bezel, Category 6, UTP, with Dust Cover, White	Almond
760238472	NETCONNECT SL Information Outlet with Clipsal bezel, Category 6, UTP, without Dust Cover, White	Black
760238471	NETCONNECT SL Information Outlet with Clipsal bezel, Category 6, UTP, without Dust Cover, Black	Black



NETCONNECT KJ SERIES INFORMATION OUTLET, WITHOUT DUST COVER, TO USE WITH KEYSTONE FACEPLATES OF OTHER SUPPLIERS

MATERIAL ID	DESCRIPTION	COLOR
2291216-1	NETCONNECT KJ Keystone Information Outlet, Category 6, UTP, without Dust Cover, Almond	Almond
2291216-2	NETCONNECT KJ Keystone Information Outlet, Category 6, UTP, without Dust Cover, Black	Black
1-2291216-3	NETCONNECT KJ Keystone Information Outlet, Category 6, UTP, without Dust Cover, White	White



NETCONNECT CATEGORY 6 U/UTP, HIGH-DENSITY SOLUTION

MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	RATE	COLOR
760237060	NPP-UDDM-SL-1U-48	NETCONNECT DDM Patch Panel, Category 6, UTP, 1U, 48 port	1U, Straight	Black
760237061	NPPA-UDDM-SL-1U-48	NETCONNECT Angled DDM Patch Panel, Category 6, UTP, 1U, 48 port	1U, Angled	Black
CO166S2-01M###		CommScope Patch cord, Category 6, 4pair, 28AWG, Stranded U/UTP, CM-LS, Black, X m	CM-LS	Black
CO166S2-02M###		CommScope Patch cord, Category 6, 4pair, 28AWG, Stranded U/UTP, CM-LS, Light Blue, X m	CM-LS	Light Blue
CO166S2-03M###		CommScope Patch cord, Category 6, 4pair, 28AWG, Stranded U/UTP, CM-LS, Gray, X m	CM-LS	Gray
CO166S2-04M###		CommScope Patch cord, Category 6, 4pair, 28AWG, Stranded U/UTP, CM-LS, Spring Green, X m	CM-LS	Spring Green
CO166S2-07M###		CommScope Patch cord, Category 6, 4pair, 28AWG, Stranded U/UTP, CM-LS, Red, X m	CM-LS	Red
CO166S2-08M###		CommScope Patch cord, Category 6, 4pair, 28AWG, Stranded U/UTP, CM-LS, White, X m	CM-LS	White
CO166S2-09M###		CommScope Patch cord, Category 6, 4pair, 28AWG, Stranded U/UTP, CM-LS, Yellow, X m	CM-LS	Yellow
CO166S2-0ZM###		CommScope Patch cord, Category 6, 4pair, 28AWG, Stranded U/UTP, CM-LS, Blue, X m	CM-LS	Blue

NOTE: Replace X with length in met. Eg: 1 = 1m, 2 = 2m, 3 = 3m, 5= 5m

Copper solutions

Category 6 U/UTP



NETCONNECT CATEGORY 6 U/UTP PATCH CORDS			
MATERIAL ID	DESCRIPTION	RATE	COLOR
NPC06UVDB-BL###F	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, CM, Blue, X ft	CM	Blue
NPC06UVDB-YL###F	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, CM, Yellow, X ft	CM	Yellow
NPC06UVDB-RD###F	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, CM, Red, X ft	CM	Red
NPC06UVDB-OR###F	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, CM, Orange, X ft	CM	Orange
NPC06UVDB-GY###F	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, CM, Gray, X ft	CM	Gray
NPC06UVDB-WT###F	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, CM, White, X ft	CM	White
NPC06UVDB-GN###F	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, CM, Green, X ft	CM	Green
NPC06UVDB-BK###F	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, CM, Black, X ft	CM	Black
NCC31URDB-08###F	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, CM, White, X ft	CMR	White
NCC31URDB-0Z###F	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, CM, Blue, X ft	CMR	Blue
NCC31URDB-0C###F	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, CM, Gray, X ft	CMR	Gray

NOTE: Replace ### with length in feet. Eg: 004 = 4F, 007 = 7F, 010 = 10F.
Stranded Cord supports length up to 30 meters. Solid Cord support length up to 100 meters.

MATERIAL ID	DESCRIPTION	RATE	COLOR
NPC06UZDB-WT###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, LSZH, White, X m	LSZH	White
NPC06UZDB-GY###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, LSZH, Gray, X m	LSZH	Gray
NPC06UZDB-OR###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, LSZH, Orange, X m	LSZH	Orange
NPC06UZDB-BL###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, LSZH, Blue, X m	LSZH	Blue
NPC06UZDB-YL###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, LSZH, Yellow, X m	LSZH	Yellow
NPC06UZDB-RD###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, LSZH, Red, X m	LSZH	Red
NPC06UZDB-GN###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded U/UTP, LSZH, Green X m	LSZH	Green
NCC37UZDB-08M###	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, LSZH, White, X m	LSZH	White
NCC37UZDB-06M###	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, LSZH, Orange, X m	LSZH	Orange
NCC37UZDB-07M###	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, LSZH, Red, X m	LSZH	Red
NCC37UZDB-09M###	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, LSZH, Yellow, X m	LSZH	Yellow
NCC37UZDB-0MM###	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, LSZH, Green, X m	LSZH	Green
NCC37UZDB-0CM###	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, LSZH, Gray, X m	LSZH	Gray
NCC37UZDB-0LM###	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, LSZH, Violet, X m	LSZH	Violet
NCC37UZDB-0ZM###	NETCONNECT Patch cord, Category 6, 4pair, Solid U/UTP, LSZH, Blue, X m	LSZH	Blue

NOTE: Replace ### with length in met. Eg: 001 = 1m, 002 = 2m, 003 = 3m, 005= 5m.
Stranded Cord supports length up to 30 meters. Solid Cord support length up to 100 meters.

Copper solutions

Category 6 F/UTP



NETCONNECT CATEGORY 6 F/UTP CABLES			
MATERIAL ID	DESCRIPTION	RATE	COLOR
874043904/10	NETCONNECT CS34P, Category 6 Cable, 4 pair, 23 AWG, F/UTP, Plenum, 1000FT, Reel, Blue	Plenum	Blue
884016408/10	NETCONNECT CS34CM, Category 6 Cable, 4 pair, 23 AWG, F/UTP, CM, 305M, Reel, white	CM	White
884033508/10	NETCONNECT CS34CM, Category 6 Cable, 4 pair, 23 AWG, F/UTP, CM, 305M, Reel, Blue	CM	Blue
884049808/10	NETCONNECT CS34Z1, Category 6 Cable, 4 pair, 23 AWG, F/UTP, LSZH, 305M, Reel, White	LSZH	White
884049858/16	NETCONNECT CS34Z1, Category 6 Cable, 4 pair, 23 AWG, F/UTP, LSZH, 500M, Reel, White	LSZH	White
884035408/10	NETCONNECT CS34Z1, Category 6 Cable, 4 pair, 23 AWG, F/UTP, LSZH, 305M, Reel, Gray	LSZH	Gray
884030004/10	NETCONNECT CS34R, Category 6 Cable, 4 pair, 23 AWG, F/UTP, LSZH, 1000FT, Reel, White	CMR	White



COMMSCOPE SL DISCRETE DISTRIBUTION MODULE (DDM) PATCH PANELS, UNLOADED					
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	SPACE	PORT	TYPE
760237046	CPP-SDDM-SL-1U-24	CommScope SL DDM Patch Panel, STP, 1U, 24 port, Straight	1U	24	Straight
760237047	CPP-SDDM-SL-2U-48	CommScope SL DDM Patch Panel, STP, 2U, 48 port Straight	2U	48	Straight
760237048	CPP-SDDM-SL-1U-24	CommScope SL DDM Patch Panel, STP, 1U, 24 port, Angled	1U	24	Angled
760237049	CPP-SDDM-SL-2U-48	CommScope SL DDM Patch Panel, STP, 2U, 48 port Angled	2U	48	Angled
760237050	CPPR-SDDM-SL-1U-24	CommScope SL DDM Patch Panel, STP, 1U, 24 port, Recessed Angled	1U	24	Recessed Angled
760237051	CPPR-SDDM-SL-2U-48	CommScope SL DDM Patch Panel, STP, 2U, 48 port, Recessed Angled	2U	48	Recessed Angled



NETCONNECT CATEGORY 6 FTP, HIGH-DENSITY SOLUTION			
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	SOLUTION
760253767	CPP-1HU-E-HD	CommScope Patch Panel, Empty, 1U	Mix Media Option
760238659	CPP-FMA-KIT-4PK	Module Adapter (4 pcs) for Fiber Adapters, Black	Mix Media Option
760243427	CPP-FMAE-KIT-4PK BLK	Fiber module adapter plus label extender (4 pcs), black	Mix Media Option
760250890	CPP-6-SDDM-SLHD-KIT-4PK	CommScope Shielded DDM for HDSL Jacks Black (4 pcs) incl ground kit and 48 HD SLX Cat 6A jacks	Mix Media Option

Copper solutions

Category 6 F/UTP



NETCONNECT SLX SERIES INFORMATION OUTLET WITH DUST COVER		
MATERIAL ID	DESCRIPTION	COLOR
2153364-1	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, with dust cover, Almond	Almond
2153364-2	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, with dust cover, Black	Black
2153364-4	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, with dust cover, Gray	Gray
2153364-5	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, with dust cover, Orange	Orange
2153364-6	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, with dust cover, Blue	Blue
2153364-7	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, with dust cover, Red	Red
2153364-8	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, with dust cover, yellow	Yellow
2153364-9	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, with dust cover, green	Green
1-2153364-3	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, with dust cover, Alpine White	Alpine White

NETCONNECT SLX SERIES INFORMATION OUTLET WITHOUT DUST COVER		
MATERIAL ID	DESCRIPTION	COLOR
2153448-1	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, without dust cover, Almond	Almond
2153448-2	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, without dust cover, Black	Black
2153448-4	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, without dust cover, Gray	Gray
2153448-5	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, without dust cover, Orange	Orange
2153448-6	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, without dust cover, Blue	Blue
2153448-7	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, without dust cover, Red	Red
2153448-8	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, without dust cover, Yellow	Yellow
2153448-9	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, without dust cover, Green	Green
1-2153448-3	AMP-TWIST SLX Series Modular Information Outlet, category 6, shielded , 4 Pair, without dust cover, Alpine White	Alpine White



NETCONNECT CATEGORY 6 F/UTP PATCH CORDS			
MATERIAL ID	DESCRIPTION	RATE	COLOR
NPC06SZDB-WT###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded S/FTP, LSZH, White, X m	LSZH	White
NPC06SZDB-GY###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded S/FTP, LSZH, Grey, X m	LSZH	Grey
NPC06SZDB-BL###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded S/FTP, LSZH, Blue, X m	LSZH	Blue
NPC06SZDB-YL###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded S/FTP, LSZH, Yellow, X m	LSZH	Yellow
NPC06SZDB-RD###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded S/FTP, LSZH, Red, X m	LSZH	Red
NPC06SZDB-GN###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded S/FTP, LSZH, Green, X m	LSZH	Green
NPC06SZDB-OR###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded S/FTP, LSZH, Orange, X m	LSZH	Orange
NPC06SZDB-BK###M	NETCONNECT Patch cord, Category 6, 4pair, Stranded S/FTP, LSZH, Black, X m	LSZH	Black

NOTE: Replace ### with length in met. Eg: 001 = 1m, 002 = 2m, 003 = 3m, 005= 5m

Copper solutions

Telephone – ADSL Systems

LSA-PLUS® DISCONNECT MODULE

MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	PAIR
60891121-02	6089 1 121-02	CommScope LSA-PLUS® Series 2 Disconnection Module, 10-pair, Contact Special Brass, Silver plated, PROFIL mounting	10
64685061-00	6468 5 061-00	Highband® Disconnection Module, category 5e, PROFIL®, 10-pair	10
64685060-08	6468 5 060-08	Highband® Ultim8 Disconnection Module, 8-pair, with jumper rings, category 6	8



LSA-PLUS® DISTRIBUTION RACK & BACKMOUNT FRAME (UNLOADED)

MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	PAIRS
Distribution Rack			
64201013-00	6420 1 013-00	LSA-PLUS® Distribution Rack, for holding standard and PROFIL modules series 2, black	1380
Backmount Frame for 19' Rack			
64271017-01	6427 1 017-01	LSA-Plus® Backmount Frame, 19 in, 15-way, 3 RU, recessed	150
64271007-01	6427 1 007-01	LSA-Plus® Backmount Frame, 19 in, 18-way, 4 RU, recessed	180
64271007-01	6427 1 007-01	LSA-Plus® Backmount Frame, 19 in, 18-way, 4 RU, recessed	180



LSA-PLUS® WALL BOXES (UNLOADED)

MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	PAIRS
64282421-00	6428 2 421-00	LSA-PLUS® Connection Box, 500 Series, holds up to 1 x 10 Series 2 LSA-PLUS modules	100
64282418-00	6428 2 418-00	LSA-PLUS® Connection Box, 500 Series, holds up to 2 x 10 Series 2 LSA-PLUS modules	200
64282419-00	6428 2 419-00	LSA-PLUS® Connection Box, 500 Series, holds up to 2 x 20 Series 2 LSA-PLUS modules	400
64282424-00	6428 2 424-00	LSA-PLUS® Connection Box, 520 Series, holds up to 2 x 34 Series 2 LSA-PLUS modules	680
64282425-00	6428 2 425-00	LSA-PLUS® Connection Box, 530 Series, holds up to 3 x 34 Series 2 LSA-PLUS modules	1020



Copper solutions

Telephone – ADSL Systems

COMPROTECT® OVERVOLTAGE PROTECTION			
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	PAIRS
EG0529-001	8800 1 010-20	1/2 ComProtect® CGB180A3 - Voice - Single pair protection plug 5-point w/ PTC - use w/ LSA series 2 (Box of 10 pcs w/ earth bar)	1
CZ7403-000	C6089 2 023-08	LSA-PLUS® Overvoltage Arrestor Magazine, 10-pair, loaded, 5kA, 230V	10

LSA-PLUS® INSERTION TOOL WITH SENSOR		
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION
64172055-01	6417 2 055-01	LSA-PLUS® Insertion Tool with Sensor



Copper solutions

Modular RJ45 Plug & Termination Tools



NETCONNECT CATEGORY 6A RJ45 MODULAR PLUG & TOOL				
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	CATEGORY	TYPE
Connector (Used with Cat6A UTP CS44 only)				
6-2843007-1	MP-6AU-Plug-A-1	Modular Plug, Category 6A/6, Unshielded, Cond Insulation OD - 0.99mm, 100/bag	Cat.6	Unshielded
2843018-3	MP-6AU-Boot-71-1:	Integrated Boot and Pair Manager for MP-6AU, 71 mm, transparent	-	Boot



TOOL KITS		
MATERIAL ID	DESCRIPTION	TYPE
2-231652-0	NETCONNECT Modular Plug Hand Tool without Dies	Tool
1-853400-5	NETCONNECT Modular Plug Die Only, 8-Position, MP-6AU Plugs, Pink Dot	Die Set



NETCONNECT CATEGORY 6 RJ45 MODULAR PLUG & TOOL			
MATERIAL ID	DESCRIPTION	CATEGORY	TYPE
6-2111979-3	NETCONNECT Modular Plug Kit, Category 6, shielded, 8-position, 5.1 – 6.0 mm max cable OD, 100/bag	Cat.6	Shielded
6-2111989-3	NETCONNECT Modular Plug Kit, Category 6, shielded, 8-position, 5.7 – 7.0 mm max cable OD, 100/bag	Cat.6	Shielded



TOOL KITS		
MATERIAL ID	DESCRIPTION	TYPE
1-790163-1	Modular Plug Hand Tool with Die for Shielded Plugs, C Size Shield (5.7 – 7.0mm)	Tool

Copper solutions

Modular RJ45 Plug & Termination Tools

TOOL KITS			
MATERIAL ID	DESCRIPTION	CATEGORY	TYPE
2-231652-1	NETCONNECT Modular Plug Hand Tool with 8-Position Die, Category 5, Black Dot	Cat.5	Tool
2-231652-0	NETCONNECT Modular Plug Hand Tool without Dies	–	Tool
1-853400-0	NETCONNECT Modular Plug Die Only, 8-Position, Category 5e, White Dot	Cat.5e	Die Set
853400-1	NETCONNECT Modular Plug Die Only, 8-Position, Category 5, Black Dot	Cat.5	Die Set



NETCONNECT MODULAR BOOT			
MATERIAL ID	DESCRIPTION	CATEGORY	COLOR
Transparent Boot, compatible with color clips			
2843048-1	NETCONNECT Modular Plug Boot, 8-Position Plug, Slim-line, Transparent, 5.7 mm max cable OD	Cat.5 & Cat.5e/ Unshielded	Transparent
2111797-1	NETCONNECT Modular Plug Boot, 8-Position Plug, Slim-line, Transparent, 6.2mm Max Cable OD	Cat.5 & Cat.5e/ Unshielded	Transparent
2843033-3	NETCONNECT Modular Plug Boot, 8-Position Plug, Slim-line, Transparent, 5.7 to 7.0 mm Cable OD	Cat.6/ Shielded	Transparent



MODULAR PLUG COLOR CLIP (USED WITH NPC PATCH CORDS)		
MATERIAL ID	DESCRIPTION	COLOR
2843022-5	NETCONNECT Modular Plug Color Clip, Orange, 50 pcs	Orange
2843022-6	NETCONNECT Modular Plug Color Clip, Blue, 50 pcs	Blue
2843022-7	NETCONNECT Modular Plug Color Clip, Red, 50 pcs	Red
2843022-8	NETCONNECT Modular Plug Color Clip, Yellow, 50 pcs	Yellow
2843022-9	NETCONNECT Modular Plug Color Clip, Green, 50 pcs	Green
2843022-1	NETCONNECT Modular Plug Color Clip, Almond, 50 pcs	Almond
2843022-2	NETCONNECT Modular Plug Color Clip, Black, 50 pcs	Black
2843022-3	NETCONNECT Modular Plug Color Clip, White, 50 pcs	White
2843022-4	NETCONNECT Modular Plug Color Clip, Gray, 50 pcs	Gray
2843022-5	NETCONNECT Modular Plug Color Clip, Orange, 50 pcs	Orange

Copper solutions

Faceplate & Accessories

FACEPLATES US STYLE			
MATERIAL ID	DESCRIPTION	PORT	COLOR
272368-1	Faceplate, single port, shutter, US style	1	Almond
272368-2	Faceplate, dual port, shutter, US style	2	Almond
760255233	Faceplate, single port, shutter, US style	1	White
760255234	Faceplate, dual port, shutter, US style	2	White
Decor Faceplate			
2-1427030-1	Decor faceplate, single port, shutter, US style	1	White
2-1427030-2	Decor faceplate, dual port, shutter, US style	2	White
2-1427030-3	Decor faceplate, triple port, shutter, US style	3	White
4 Ports Faceplate			
760249154	Faceplate, labeled, 1-gang, 4 port, US style, universal opening	4	Light Almond
760249146	Faceplate, labeled, 1-gang, 4 port, US style, universal opening	4	Prowhite
Angled Faceplate			
1-1375155-3	Faceplate, 2 port, angled, flush mount, US style	2	White

FACEPLATES UK STYLE	
MATERIAL ID	DESCRIPTION
760249249	Faceplate Kit, 1 port, universal opening port, BS, White
760249251	Faceplate Kit, 2 ports, universal opening port, BS, White
760249253	Faceplate Kit, 4 ports, universal opening port, BS, White
760253100	Faceplate Kit, 1 port, universal opening port, BS, unshuttered, White
760249256	Faceplate Kit, 2 port, universal opening port, BS, unshuttered, White
760254617	Faceplate Kit, 4 port, universal opening port, BS, unshuttered, White



SINGLE AND DUAL OUTLETS 45 X 45 MM ("MOSAIC"), USED WITH LEGRAND FACEPLATE		
MATERIAL ID	DESCRIPTION	COLOR
1711276-1	Dual Port Outlet, shuttered flat, for 2 SL information outlets, 45 x 45 mm	White
1711277-1	Single Port Outlet, shuttered flat, for 1 SL information outlet, 45 x 45 mm	White
1711349-1	Single Port Outlet, shuttered flat, for 1 SL information outlet, 22.5 x 45 mm	White



Copper solutions

Faceplate & Accessories



BOXES		
MATERIAL ID	DESCRIPTION	COLOR
Surface & Ceiling Mount Box		
760248524	Surface Mount Office Box, universal opening port, 1 port, unloaded	Almond
760248528	Surface Mount Office Box, universal opening port, 2 port, unloaded	Almond
760248523	Surface Mount Office Box, universal opening port, 1 port, unloaded	Prowhite
760248527	Surface Mount Office Box, universal opening port, 2 port, unloaded	Prowhite
Zone Box		
1933671-2	Surface Mount Module, 4 port	Black
1933674-2	Surface Mount Module, 6 port	Black
1479358-2	Surface Mount Module, 12 port	Black
1479398-1	Surface Mount Module Magnet (used with 1479358-2)	Black
Meeting Room Solution		
1-1671163-1	Consolidation Point Enclosure, 4-port, twist/SL information outlet	Black
2111500-2	SL Series HDMI Coupler Insert	Black
1-1499836-1	SL Series, Adapter SC Simplex, Single-mode/Multimode	Almond
1933286-6	SL Fiber Optic Insert Adapter, LC, duplex, singlemode/multimode	Aqua
1933286-4	SL Fiber Optic Insert Adapter, LC, duplex, singlemode/multimode	Blue

Copper solutions

Faceplate & Accessories



CONSOLIDATION POINT			
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	MODULE
UTP Copper (Support Cat6A, Cat6, Cat5e)			
64501105-21	6450 1 105-21	Highband® Consolidation Point, category 6A, 100-pair	100 Pairs
Mixed Copper & Fiber Box			
406771-1		Consolidation point assembly (unloaded)	4
1479322-1		Consolidation point assembly, center feed, dual support, foor box (unloaded)	6
1479696-1		Unshielded Multimedia Module, 6 ports, accepts SL Series inserts	1
1499836-9		SL Series, Adapter SC Simplex, Single-mode/Multimode, Green	-



NETCONNECT SL TOOL	
MATERIAL ID	DESCRIPTION
1725150-6	SL SERIES INFORMATION OUTLET TOOL KIT - LARGE DIA

Copper solutions

Horizontal Cable Management

HORIZONTAL CABLE MANAGEMENT	
MATERIAL ID	DESCRIPTION
760072942	CommScope Cable Management Panel, Horizontal, Metal Finger Duct, 1U, black
760072959	CommScope Cable Management Panel, Horizontal, Metal Finger Duct, 2U, black
760038240	CommScope Cable Management Panel, Horizontal, Metal 4 Ring, 1U, black



760072942



760072959



760038240

Copper solutions

Outdoor Application

NETCONNECT CATEGORY 6			
MATERIAL ID	DESCRIPTION	JACKET	TYPE
1427319-1	NETCONNECT Category 6, 4 pair, 23AWG, U/UTP, PE, 1000ft, Pull-box, black	PE	U/UTP



NETCONNECT CATEGORY 6A F/UTP			
MATERIAL ID	DESCRIPTION	JACKET	TYPE
CO11192-01F###	NETCONNECT Patch cord, Category 6A, 4pair, Stranded F/UTP, LSZH, Black, X ft	PE	F/UTP

NOTE: Replace ### with length in feet. Eg: 004 = 4F, 007 = 7F, 010 = 10F

Powered Fiber solutions

POWERED FIBER CABLE SYSTEM

- Outdoor and riser/LSZH, indoor/outdoor rated versions
- SELV and NEC Class 2 compliant
- Fast “banana peel” style cable access
- Utilizes globally existing, proven and inexpensive FTTH-style flat cable hardware



COMMSCOPE POWERED FIBER CABLE SYSTEM	
MATERIAL ID	DESCRIPTION
PFC-S02L12	Powered Fiber Cable, Indoor/Outdoor, OS2, 2 Fibers, 2 x 12 AWG Conductors
PFC-S02L16	Powered Fiber Cable, Indoor/Outdoor, OS2, 2 Fibers, 2 x 16 AWG Conductors
PFC-S02O12	Powered Fiber Cable, Outdoor, OS2, 2 Fibers, 2 x 12 AWG Conductors
PFC-S02O16	Powered Fiber Cable, Outdoor, OS2, 2 Fibers, 2 x 16 AWG Conductors
PFC-S04L12	Powered Fiber Cable, Indoor/Outdoor, OS2, 4 Fibers, 2 x 12 AWG Conductors
PFC-S04L16	Powered Fiber Cable, Indoor/Outdoor, OS2, 4 Fibers, 2 x 16 AWG Conductors
PFC-S04O12	Powered Fiber Cable, Outdoor, OS2, 4 Fibers, 2 x 12 AWG Conductors
PFC-S04O16	Powered Fiber Cable, Outdoor, OS2, 4 Fibers, 2 x 16 AWG Conductors
PFC-S12L12	Powered Fiber Cable, Indoor/Outdoor, OS2, 12 Fibers, 2 x 12 AWG Conductors
PFC-S12L16	Powered Fiber Cable, Indoor/Outdoor, OS2, 2 Fibers, 12 x 16 AWG Conductors
PFC-S12O12	Powered Fiber Cable, Outdoor, OS2, 12 Fibers, 2 x 12 AWG Conductors
PFC-S12O16	Powered Fiber Cable, Outdoor, OS2, 12 Fibers, 2 x 16 AWG Conductors
PFC-302L12	Powered Fiber Cable, Indoor/Outdoor, OM3, 2 Fibers, 2 x 12 AWG Conductors
PFC-302L16	Powered Fiber Cable, Indoor/Outdoor, OM3, 2 Fibers, 2 x 16 AWG Conductors
PFC-302O12	Powered Fiber Cable, Outdoor, OM3, 2 Fibers, 2 x 12 AWG Conductors
PFC-302O16	Powered Fiber Cable, Outdoor, OM3, 2 Fibers, 2 x 16 AWG Conductors
PFC-304L12	Powered Fiber Cable, Indoor/Outdoor, OM3, 4 Fibers, 2 x 12 AWG Conductors
PFC-304L16	Powered Fiber Cable, Indoor/Outdoor, OM3, 4 Fibers, 2 x 16 AWG Conductors
PFC-304O12	Powered Fiber Cable, Outdoor, OM3, 4 Fibers, 2 x 12 AWG Conductors
PFC-304O16	Powered Fiber Cable, Outdoor, OM3, 4 Fibers, 2 x 16 AWG Conductors

Powered Fiber solutions

1 AND 2-PORT POE EXTENDERS

- IP68 sealing—Enclosures are designed for outdoor installations with protection from moisture and the environment
- Automatically corrects for distance voltage drop in the hybrid cable
- Integrated Electrical Protection
- 60W 2-port variant enables 2 PoE or PoE+ devices to be connected via one hybrid cable.
- 60W single port variation supports 802.3bt, Class 6 power levels. It can be equipped with SPF+ transceivers, and deliver 5 Gbps Ethernet over the copper port.

MATERIAL ID	DESCRIPTION
PFU-P-C-O-060-02	60W, 2 Port PoE Extender*
PFU-P-E-O-060-01	60W, 1 Port 5 Gbps PoE Extender

*The 60W, 2-port PoE Extender provides a maximum of 30W on each port.

POWER EXTENDERS/FIBER PASS-THRU

- Provide the same power management and electrical protection benefits of the PoE Extenders.
- Designed to handle devices which require direct fiber input and DC power.
- IP68 sealing—Enclosures are designed for outdoor installations with protection from moisture and the environment

MATERIAL ID	DESCRIPTION
PFU-48-C-O-060-01	Power extender fiber pass through 48VDC
PFU-12-C-O-060-01	Power extender fiber pass through 12VDC

POWER SUPPLIES

- 57VDC Power Supply for use with Powered Fiber Cable System

MATERIAL ID	DESCRIPTION
PFP-PX-S1	Power Express Distribution shelf with alarm module
PFP-PX-8M	Power Express Distribution module supports max. 8 Devices
PFP-PX-SF	Power Express Blank Slot Panel
PFP-SPS-S1	SPS Rectifier Power Distribution Shelf
PFP-SPS-1600M	1600W SPS Power Rectifier module
PFP-SPS-C1	SPS Rectifier Controller Display
PFP-SPS-SF	SPS Rectifier Blank Slot Panel



PFU-P-C-O-060-02



PFU-48-C-O-060-01



Powered Fiber solutions

SURFACE MOUNT BOXES


- Supports structured cabling labeling and administration
- Protects your powered fiber cable and connections
- Provides a clean end point to terminate new indoor plenum powered fiber cables.
- Supports multigig Wi-Fi access points.
- Supports new and existing powered fiber cables




MATERIAL ID	DESCRIPTION
760248944	Kit, SMB, 1 Fiber Port, 1 Power Port, Beige
760248943	Kit, SMB, 1 Fiber Port, 1 Power Port, White
760248942	Kit, SMB, 1 Fiber Port, 1 Power Port, Black
760249095	Kit, SMB, 2 Fiber Ports, 2 Power Ports, Beige
760249094	Kit, SMB, 2 Fiber Ports, 2 Power Ports, White
760249093	Kit, SMB, 2 Fiber Ports, 2 Power Ports, Black

PLENUM POWERED FIBER CABLE TRANSITION BOX

- Provides easy and secure transition point for indoor to outdoor powered fiber cables
- Termination point for permanent link powered fiber cables for future end-device installations
- Plenum rated enclosure
- Dimensions: 4.37 in (111 mm) x 14.18 in (360 mm) x 14.57 in (370 mm)
- Interface features, inside: (6) fiber LC duplex, (6) two wire terminals
- Interface capacity: 6 channels
- Surface mounted
- Input Power: 100 W per channel (NEC Class 2)
- Input voltage: 30 Vac | 60 Vdc per channel
- Safety Standards: UL2043 | UL1863 | UL62360 | CE
- Environmental Space: Indoor | Plenum
- Weight: 14 lbs (6.35 kg)
- Package quantity: 1



MATERIAL ID	DESCRIPTION
760250853	PFC Transition Box, Plenum rated, cool gray



The FiberGuide® fiber management systems offers the greatest breadth of optical raceway products in the industry. It is designed to protect and route fiber optic patch cords, multi-fiber cable assemblies and intrafacility fiber cable (IFC) to and from fiber splice enclosures, fiber distribution frames and fiber optic terminal devices.

Tool-less, Snap-Fit™ junctions significantly reduce the amount of time required for installation. FiberGuide is available in a variety of sizes and basic components include horizontal and vertical straight sections, horizontal and vertical elbows, downspouts, junctions and numerous support hardware and flex-vertical kits.

Available in a variety of sizes: 50x50, 50x150, 100x100, 100x150, 100x300, and 100x600. Below is a selection of our 100x150, 100x300 and 100x600 systems. For more sizes and options, [please download the full catalog.](#)

STRAIGHT SECTIONS & FITTINGS			
DESCRIPTION	100x150mm	100x300mm	100x600mm
Straight Section Horizontal - L= 1,83 mtr	FGS-MSHS-B	FGS-MSHS-F	FGS-MSHS-H
Straight Section Cover	FGS-MSNC-B/G	FGS-MSNC-F	FGS-FSFC-H
Horizontal Cross	FGS-MHXP-B	FGS-MHXP-F	FGS-MHXP-H
Horizontal Cross Cover	FGS-SHXP-B	FGS-SHXP-F	FGS-FHXP-H
T-Adapter - Horizontal	FGS-MHRT-B	FGS-MHRT-F	FGS-MHRT-H
90° Elbow - Horizontal	FGS-MH9E-B	FGS-MH9E-F	
90° Elbow Vertical - Up With Cover	FGS-MU9E-B		
90° Elbow Vertical - Down	FGS-MD9E-B	FGS-MD9E-F	
45° Elbow - Horizontal	FGS-MH4E-B	FGS-MH4E-F	FGS-MH4E-H
45° Elbow Vertical - Up With Cover	FGS-MU4E-B	FGS-MU4E-F	FGS-MU4E-H
45° Elbow Vertical - Down	FGS-MD4E-B	FGS-MD4E-F	FGS-MD4E-H
Trumpet Flare	FGS-MTRM-B	FGS-MTRM-F	FGS-MTRM-H
End Cap	FGS-HMEC-B	FGS-HMEC-F	FGS-HMEC-H

JUNCTIONS			
DESCRIPTION	100x150mm	100x300mm	100x600mm
Junctions/Joiners	FGS-MFAW-B	FGS-MFAW-F	FGS-MFAW-H

FIXED DOWNSPOUTS			
DESCRIPTION	100x150mm	100x300mm	100x600mm
Downspout kit	FGS-MDSP-B	FGS-MDSP-F	
Cover	FGS-MCDS-AB	FGS-SDSP-F	

EXPRESS EXIT DOWNSPOUTS

DESCRIPTION	100x150mm	100x300mm	100x600mm
50mm Express Exit™	FGS-MEXP-A/B/F	FGS-MEXP-A/B/F	FGS-MEXP-A/B/F
50mm Low-profile Express Exit™	FGS-MEXP-LP-A/B/F	FGS-MEXP-LP-A/B/F	FGS-MEXP-LP-A/B/F
100mm Express Exit™	FGS-MEXP-E-A/B/F	FGS-MEXP-E-A/B/F	FGS-MEXP-E-A/B/F
Express Exit Rear Hinged Cover for 100x300 Raceway, Yellow		FGS-MEXC-E-F	
300mm Express Exit™, No Cover		FGS-MEXP-F-F/H-NC	FGS-MEXP-F-F/H-NC

DOWNSPOUT ACCESSORIES

DESCRIPTION	100x150mm	100x300mm	100x600mm
Single 50mm Flex Tube Attachment, 50x50mm	FGS-MEX1-C-0F	FGS-MEX1-C-0F	FGS-MEX1-C-0F
Single 50mm Flex Tube Attachment, 100x100mm	FGS-KT03-A1NH	FGS-KT03-A1NH	FGS-KT03-A1NH
Dual 50mm Flex Tube Attachment, 100x100mm	FGS-KT03-ANH	FGS-KT03-ANH	FGS-KT03-ANH
Dual 50mm Flex Tube Attachment, 100x150mm	FGS-KT03-B-0F	FGS-KT03-B-0F	FGS-KT03-B-0F
50mm Flex Tube, Slotted (x= length in feet 5, 10, 15, 20, 25, 30, 35, 40, 45, 50....)	FGS-MIDY-xF	FGS-MIDY-xF	FGS-MIDY-xF
FlexVertical Kit, 50x50mm, 1219mm length	FGS-FLEXV-4F-C	FGS-FLEXV-4F-C	FGS-FLEXV-4F-C
FlexVertical Kit, 50x50mm, 2133mm length	FGS-FLEXVAD-7F-C	FGS-FLEXVAD-7F-C	FGS-FLEXVAD-7F-C
FlexVertical Dual Kit, 100x100mm to Dual 50x50mm, 1219mm length	FGS-FLEXV-4F-A2C	FGS-FLEXV-4F-A2C	FGS-FLEXV-4F-A2C

BRACKETS FOR THREADED RODS

DESCRIPTION	100x150mm	100x300mm	100x600mm
New Threaded Rod Bracket 12mm	FGS-HNTR-12MM	FGS-HNTR-F-12MM	
New Threaded Rod Bracket 16mm		FGS-HNTP-F-16MM	FGS-HNTP-H-16MM
Trapeze Support Bracket 12mm		FGS-HNTP-F-12MM	
C- Bracket Threaded Rod 12mm	FGS-HNTS-12MM	FGS-HNTS-F-12MM	FGS-HNTS-H-12MM-A
C- Bracket Threaded Rod 16mm	FGS-HNTS-16MM	FGS-HNTS-F-16MM	

TOOLS

DESCRIPTION	100x150mm	100x300mm	100x600mm
Mitre Box with Saw for 50, 100, 150 & 300mm Straight Section	FGS-MKIT-ABF	FGS-MKIT-ABF	FGS-MKIT-H

Fiber solutions

Fiber Optic Cable



COMMScope INDOOR, LSZH & OFNR DUAL RATE CABLE - APAC


FIBER CORE	CABLE TYPE	OM5	OM4	OM3	SM
2	CommScope Fiber Optic Cable, Indoor, LSZH & OFNR,, 2 Fibers	–	760249363	760249357	760249369
4	CommScope Fiber Optic Cable, Indoor, LSZH & OFNR, 4 Fibers	–	760249364	760249358	760249370
6	CommScope Fiber Optic Cable, Indoor, LSZH & OFNR, 6 Fibers	–	760249365	760249359	760249371
8	CommScope Fiber Optic Cable, Indoor, LSZH & OFNR, 8 Fibers	–	760249366	760249360	760249372
12	CommScope Fiber Optic Cable, Indoor, LSZH & OFNR, 12 Fibers	–	760249367	760249361	760249373
24	CommScope Fiber Optic Cable, Indoor, LSZH & OFNR, 24 Fibers	–	760249368	760249362	760249374
48	CommScope Fiber Optic Cable, Indoor, LSZH & OFNR, 48 Fibers	–	760250119	760250122	760250125
72	CommScope Fiber Optic Cable, Indoor, LSZH & OFNR, 72 Fibers	–	760250121	760250118	760250120
96	CommScope Fiber Optic Cable, Indoor, LSZH & OFNR, 96 Fibers	–	760250123	760250124	760250117

COMMScope INDOOR, OFNP DISTRIBUTION CABLE - APAC

FIBER CORE	CABLE TYPE	OM5	OM4	OM3	SM
2	CommScope Fiber Optic Cable, Indoor, OFNP, 2 Fibers	760255261	760255257	760255255	760255259
4	CommScope Fiber Optic Cable, Indoor, OFNP, 4 Fibers	760255262	760255258	760255256	760255260
6	CommScope Fiber Optic Cable, Indoor, OFNP, 6 Fibers	760253573	760248757	760251671	760249758
8	CommScope Fiber Optic Cable, Indoor, OFNP, 8 Fibers	760253574	760249029	760251670	760249759
12	CommScope Fiber Optic Cable, Indoor, OFNP, 12 Fibers	760253575	760249030	760251669	760249760
24	CommScope Fiber Optic Cable, Indoor, OFNP, 24 Fibers	760253576	760249031	760251668	760249761

Fiber solutions

Fiber Optic Cable



COMMSCOPE INDOOR/OUTDOOR GEL LSZH CENTRAL TUBE CABLE – APAC

FIBER CORE	DESCRIPTION	OM4	OM3	SM
2	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 2 Fibers	760251948	760251945	760251942
4	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 4 Fibers	760251949	760251946	760251943
8	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 8 Fibers	760251950	760251947	760251944
6	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 6 Fibers	760249716	760249713	760249710
12	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 12 Fibers	760249717	760249714	760249711
24	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 24 Fibers	760249718	760249715	760249712

COMMSCOPE INDOOR/OUTDOOR GEL LSZH STRANDED LOOSE TUBE CABLE – APAC

FIBER CORE	DESCRIPTION	OM4	OM3	SM
24	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 24 Fibers	760251966	760251964	760251960
36	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 36 Fibers	760251967	760251965	760251961
48	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 48 Fibers	760249744	760249742	760249740
72	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 72 Fibers	760249745	760249743	760249741
96	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 96 Fibers			760251962
144	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 144 Fibers			760251963

COMMSCOPE INDOOR/OUTDOOR GEL LSZH CENTRAL LOOSE TUBE CABLE, ARMORED – APAC


FIBER CORE	DESCRIPTION	OM4	OM3	SM
2	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 2 Fibers	760251957	760251954	760251951
4	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 4 Fibers	760251958	760251955	760251952
8	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 8 Fibers	760251959	760251956	760251953
6	CommScope Fiber Optic Cable, Indoor/OutDoor, CST LSZH, 6 Fibers	760249725	760249722	760249719
12	CommScope Fiber Optic Cable, Indoor/OutDoor, CST LSZH, 12 Fibers	760249726	760249723	760249720
24	CommScope Fiber Optic Cable, Indoor/OutDoor, CST LSZH, 24 Fibers	760249727	760249724	760249721

COMMSCOPE INDOOR/OUTDOOR GEL LSZH STRANDED LOOSE TUBE CABLE, ARMORED – APAC

FIBER CORE	DESCRIPTION	OM4	OM3	SM
24	CommScope Fiber Optic Cable, Indoor/OutDoor, CST LSZH, 24 Fibers	760251974	760251972	760251968
36	CommScope Fiber Optic Cable, Indoor/OutDoor, CST LSZH, 36 Fibers	760251975	760251973	760251969
48	CommScope Fiber Optic Cable, Indoor/OutDoor, CST LSZH, 48 Fibers	760249750	760249748	760249746
72	CommScope Fiber Optic Cable, Indoor/OutDoor, CST LSZH, 72 Fibers	760249751	760249749	760249747
96	CommScope Fiber Optic Cable, Indoor/OutDoor, CST LSZH, 96 Fibers			760251970
144	CommScope Fiber Optic Cable, Indoor/OutDoor, CST LSZH, 144 Fibers			760251971

Fiber solutions

Fiber Optic Cable




COMMSCOPE INDOOR/OUTDOOR LSZH DISTRIBUTION CABLE				
FIBER CORE	DESCRIPTION	OM4	OM3	SM
4	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 4 Fibers	760238329	760046649	760068718
6	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 6 Fibers	760039974	760039966	760009753
8	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 8 Fibers	760039982	760031674	760073403
12	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 12 Fibers	760006650	700210982	760004184
24	CommScope Fiber Optic Cable, Indoor/OutDoor, LSZH, 24 Fibers	760070300	760070292	760070276



COMMSCOPE INDOOR/OUTDOOR, FIGURE 8 DROP CABLE - APAC		
FIBER CORE	DESCRIPTION	SM
2	CommScope Fiber Optic Cable, Indoor/Outdoor, Figure 8 Drop, 2 Fibers	760254876
4	CommScope Fiber Optic Cable, Indoor/Outdoor, Figure 8 Drop, 4 Fibers	760254877

Fiber solutions

Fiber Optic Cable



COMMSCOPE OSP GEL CENTRAL TUBE CABLE - APAC

FIBER CORE	DESCRIPTION	OM4	OM3	SM
2	CommScope Fiber Optic Cable, Outside Plant, 2 Fibers	760252025	760252022	760252019
4	CommScope Fiber Optic Cable, Outside Plant, 4 Fibers	760252026	760252023	760252020
8	CommScope Fiber Optic Cable, Outside Plant, 8 Fibers	760252027	760252024	760252021
6	CommScope Fiber Optic Cable, Outside Plant, 6 Fibers	760249698	760249695	760249692
12	CommScope Fiber Optic Cable, Outside Plant, 12 Fibers	760249699	760249696	760249693
24	CommScope Fiber Optic Cable, Outside Plant, 24 Fibers	760249700	760249697	760249694

COMMSCOPE OSP GEL LOOSE TUBE CABLE - APAC

FIBER CORE	DESCRIPTION	OM4	OM3	SM
24	CommScope Fiber Optic Cable, Outside Plant, 24 Fibers	760252043	760252041	760252037
36	CommScope Fiber Optic Cable, Outside Plant, 36 Fibers	760252044	760252042	760252038
48	CommScope Fiber Optic Cable, Outside Plant, 48 Fibers	760249732	760249730	760249728
72	CommScope Fiber Optic Cable, Outside Plant, 72 Fibers	760249733	760249731	760249729
96	CommScope Fiber Optic Cable, Outside Plant, 96 Fibers			760252039
144	CommScope Fiber Optic Cable, Outside Plant, 144 Fibers			760252040

COMMSCOPE OSP GEL CENTRAL TUBE CABLE, ARMORED - APAC

FIBER CORE	DESCRIPTION	OM4	OM3	SM
2	CommScope Fiber Optic Cable, Outside Plant, CST, 2 Fibers	760252034	760252031	760252028
4	CommScope Fiber Optic Cable, Outside Plant, CST, 4 Fibers	760252035	760252032	760252029
8	CommScope Fiber Optic Cable, Outside Plant, CST, 8 Fibers	760252036	760252033	760252030
6	CommScope Fiber Optic Cable, Outside Plant, CST, 6 Fibers	760249707	760249704	760249701
12	CommScope Fiber Optic Cable, Outside Plant, CST, 12 Fibers	760249708	760249705	760249702
24	CommScope Fiber Optic Cable, Outside Plant, CST, 24 Fibers	760249709	760249706	760249703

COMMSCOPE OSP GEL LOOSE TUBE CABLE, ARMORED - APAC

FIBER CORE	DESCRIPTION	OM4	OM3	SM
24	CommScope Fiber Optic Cable, Outside Plant, CST, 24 Fibers	760252051	760252049	760252045
36	CommScope Fiber Optic Cable, Outside Plant, CST, 36 Fibers	760252052	760252050	760252046
48	CommScope Fiber Optic Cable, Outside Plant, CST, 48 Fibers	760249738	760249736	760249734
72	CommScope Fiber Optic Cable, Outside Plant, CST, 72 Fibers	760249739	760249737	760249735
96	CommScope Fiber Optic Cable, Outside Plant, CST, 96 Fibers			760252047
144	CommScope Fiber Optic Cable, Outside Plant, CST, 144 Fibers			760252048

Fiber Panel Portfolios

Panel, Wall Boxes and Accessories



The G2 family of panels and modules is a versatile solution that is available in configurations for any application. No matter what polarity, fiber count or performance needed, the G2 family has a solution.

The EPX panel is a low-cost solution for usable density in a 1U format.

G2 PANELS				
Density	Series	Material ID	Product Number	Description
96 LC/RU 32 MPO/RU	EPX Simple & Cost Effective	760241517	EPX-1U-MOD-OPEN-F-FX	EPX Foldable Arm Open Rear Fixed, Flat Plate
		760241518	EPX-1U-MOD-OPEN-F-ANG-FX	EPX Foldable Arm Open Rear Fixed, Angled Plate
	EPX - Express Compact & Flexible	760254918	EPX-1U-MOD-OPEN	EPX 1U G2 Open Sliding Fiber Panel
		760251098	EPX-1U-MOD-OPEN-FX	EPX 1U G2 Open Fixed Fiber Panel
		760249998	EPX-1U-MOD-ENC	EPX 1U G2 Enclosed Sliding Fiber Panel
		760251044	EPX-2U-MOD-ENC	EPX 2U G2 Enclosed Sliding Fiber Panel
		760251048	EPX-4U-MOD-ENC	EPX 4U G2 Enclosed Sliding Fiber Panel
		760251042	EPX-1U-MOD-ENC-FX	EPX 1U G2 Enclosed Fixed Fiber Panel
		760251046	EPX-2U-MOD-ENC-FX	EPX 2U G2 Enclosed Fixed Fiber Panel
760251050	EPX-4U-MOD-ENC-FX	EPX 4U G2 Enclosed Fixed Fiber Panel		

Wall Mount Building Enclosures provide fiber distribution management when space is at a premium. The WBE-MOD's are compatible will all G2 modules and adapter packs.

G2 WALL BOXES			
Density	Material ID	Description	
24 LC	760248900	WB2-EMT-BK-1P-MOD	
48 LC	760248901	WB2-EMT-BK-2P-MOD	
96 LC	760248902	WB2-EMT-BK-4P-MOD	
192 LC	760248903	WB2-EMT-BK-8P-MOD	



WB2-EMT-BK-2P-MOD

G2 ACCESSORIES		
EPX Panel Accessories		
760241378	EPX-SPLICE-48	EPX Splice Tray Kit
Miscellaneous		
760209619	CABLE-MOUNT-KIT-12	Cable attachment molding x 12
760058677	RMB-6-1/2	InstaPATCH Plus attachment bracket, rack mounted, six 1/2" fittings
760058685	RMB-6-3/8	InstaPATCH Plus attachment bracket, rack mounted, six 3/8" fittings
760109462	360G2-MOD-BLANK-4PK	Mod Panel Blank Adapter Pack, 4 Panels
760242678	Patch cord fitting kit with 12 cable glands	Gland to fix multiple MPO patchcords on HD/UD/EHD, 12 packs
760242679	Trunk fitting kit with 12 cable glands	Gland to fix multiple MPO 12/24F trunks on HD/UD/EHD, 12 packs



EPX-SPLICE-48

Fiber Panel Portfolios

G2 Modules



G2 MODULES - METHOD A						
	MPO 12 - 12 Fiber		MPO 12 - 24 Fiber		MPO 24 - 24 Fiber	
	Material ID	Product Number	Material ID	Product Number	Material ID	Product Number
LC Multimode (OM3-OM4)	760242493	DM12-12LC-LS-A	760242495	DM12-24LC-LS-A	760242497	DM24-24LC-LS-A
	760242494	DM12-12LC-LS-AF	760242496	DM12-24LC-LS-AF	760242502	DM24-24LC-LS-AF
LC Singlemode UPC	760242498	DM12-12LC-SM-A	760242500	DM12-24LC-SM-A	X	X
	760242499	DM12-12LC-SM-AF	760242501	DM12-24LC-SM-AF	X	X
LC Singlemode APC	760244686	DM12-12LCA-SM-A	760244688	DM12-24LCA-SM-A	X	X
	760244687	DM12-12LCA-SM-AF	760244689	DM12-24LCA-SM-AF	X	X
SC Singlemode APC	760245425	DM12-12SCA-SM-A	X	X	X	X
	760245426	DM12-12SCA-SM-AF	X	X	X	X



G2 CONVERSION MODULES- METHOD A		
	Material ID	Product Number
MPO12 (2) / MPO8 (3) OM4	760245325	CM12-2X3-LS-A
MPO12 (2) / MPO8 (3) OM4	760245326	CM12-2X3-LS-AF
MPO24 (1) / MPO8 (3) OM4	760245327	CM24-1X3-LS-A
MPO24 (2) / MPO8 (6) OM4	760245328	CM24-2X6-LS-A

Fiber Panel Portfolios

G2 Splice Cassettes



G2 SPLICE CASSETTES WITH PIGTAILS

Multimode		
Material ID	Product Number	Description
760244927	G2-SP-24LCX-PT	Splicing cassette, 24LC, OM4, pigtail
760245398	G2-SP-24LCV-PT	Splicing cassette, 24LC, OM5, pigtail
760245399	G2-SP-12LCX-PT	Splicing cassette, 12LC, OM4, pigtail
760245403	G2-SP-12LCV-PT	Splicing cassette, 12LC, OM5, pigtail
760248831	G2-SP-12SCX-PT	Splicing cassette, 12SC, OM4, pigtail
760244928	G2-SP-24LCX-RPT	Splicing cassette, 24LC, OM4, ribbon pigtail
760245400	G2-SP-12LCX-RPT	Splicing cassette, 12LC, OM4, ribbon pigtail
Singlemode		
760244929	G2-SP-24LCG-PT	Splicing cassette, 24LC, singlemode, pigtail
760245961	G2-SP-24LAG-PT	Splicing cassette, 24LC/APC, singlemode, pigtail
760245401	G2-SP-12LCG-PT	Splicing cassette, 12LC, singlemode, pigtail
760245960	G2-SP-12LAG-PT	Splicing cassette, 12LC/APC, singlemode, pigtail
760245963	G2-SP-12SCG-PT	Splicing cassette, 12SC/UPC, singlemode, pigtail
760245962	G2-SP-12SAG-PT	Splicing cassette, 12SC/APC, singlemode, pigtail
760234930	G2-SP-24LCG-RPT	Splicing cassette, 24LC, singlemode, ribbon pigtail
760245402	G2-SP-12LCG-RPT	Splicing cassette, 12LC, singlemode, ribbon pigtail



G2 SPLICE CASSETTES WITHOUT PIGTAIL

Material ID	Product Number	Description
760245494	G2-SP-24LC	Splicing cassette, 24LC, no pigtail
760245495	G2-SP-12LC	Splicing cassette, 12LC, no pigtail
760245496	G2-SP-12SC	Splicing cassette, 12SC, no pigtail
760245497	G2-SP-0000	Splicing cassette, no adapter, no pigtail

Fiber Panel Portfolios

G2 Adapter Packs



360DPis-24LC-LS

G2 ADAPTER PACKS				
	12 Fiber		24 Fiber	
	Material ID	Product Number	Material ID	Product Number
LC Multimode (OM3-OM4)	760230938	360DPis-12LC-LS	760216754	360DPis-24LC-LS
LC Multimode (OM5)	760236043	360DPis-12LC-WB	760236041	360DPis-24LC-WB
LC Singlemode	760230946	360DPis-12LC-SM	760216762	360DPis-24LC-SM
LC Singlemode APC	760230961	360DPis-12LCA-SM	760216770	360DPis-24LCA-SM
SC Multimode (OM3-OM4)	760134551	360DP-12SC-LS	X	X
SC Singlemode	760135087	360DP-12SC-SM	X	X
SC Singlemode APC	760135095	360DP-12SCA-SM	X	X



360DP-2MPO



360DP-4MPO



360DP-6MPO-BK



360DP-8MPO

G2 MPO ADAPTER PACKS - METHOD B		
	Material ID	Product Number
2 MPO	760107490	360DP-2MPO
4 MPO	760107508	360DP-4MPO
6 MPO	760107516	360DP-6MPO
8 MPO	760107524	360DP-8MPO

G2 MPO ADAPTER PACKS - METHOD A		
	Material ID	Product Number
2 MPO	760243438	360DP-2MPO-A
4 MPO	760243439	360DP-4MPO-A
6 MPO	760242723	360DP-6MPO-A
8 MPO	760242724	360DP-8MPO-A

Fiber Panel Portfolios

Standard Density Fiber Solutions



EPX Standard density fiber optic panels were specifically designed to make your building's infrastructure effective, efficient and easier to manage. This solutions deliver high performance through modular and easy-to use pigtailed splicing cassettes. The LGX/1000 style splice cassettes are designed for individual pigtails, each pre-loaded and pre-routed for quick fusion splicing. These cassettes provide a protective space for fusion splicing, patching and storing your fiber optic cables. By incorporating these advantages into a single cassette, you can be confident that your connections and cabling will be safeguarded from contamination or future damage.

LGX/1000 STYLE PANELS

Density	Solution	Material ID	Product Number	Description
72 LC / RU	EPX - Express Compact & Flexible	760254919	EPX-1U-PNL-OPEN	EPX 1U LGX/1000 STYLE Open Sliding Fiber Panel
		760251099	EPX-1U-PNL-OPEN-FX	EPX 1U LGX/1000 STYLE Open Fixed Fiber Panel
		760249997	EPX-1U-PNL-ENC	EPX 1U LGX/1000 STYLE Enclosed Sliding Fiber Panel
		760251045	EPX-2U-PNL-ENC	EPX 2U LGX/1000 STYLE Enclosed Sliding Fiber Panel
		760251049	EPX-4U-PNL-ENC	EPX 4U LGX/1000 STYLE Enclosed Sliding Fiber Panel
		760251043	EPX-1U-PNL-ENC-FX	EPX 1U LGX/1000 STYLE Enclosed Fixed Fiber Panel
		760251047	EPX-2U-PNL-ENC-FX	EPX 2U LGX/1000 STYLE Enclosed Fixed Fiber Panel
		760251051	EPX-4U-PNL-ENC-FX	EPX 4U LGX/1000 STYLE Enclosed Fixed Fiber Panel

LGX/1000 STYLE WALL BOXES

Description	Material ID	Product Number
24 LC	760248904	WB2-EMT-BK-1P-PNL
48 LC	760248905	WB2-EMT-BK-2P-PNL
96 LC	760248906	WB2-EMT-BK-4P-PNL
192 LC	760248907	WB2-EMT-BK-8P-PNL




LGX/1000 STYLE SPLICING CASSETTE

Type	12 LC		24LC		12 SC	
	Material ID	Product Number	Material ID	Product Number	Material ID	Product Number
With Pigtail						
OM4	760221739	PNL-CS-12LCX-PT	760221697	PNL-CS-24LCX-PT	760221770	PNL-CS-12SCX-PT
OM5	760242108	PNL-CS-12LCV-PT	760242109	PNL-CS-24LCV-PT	-	-
SM UPC	760221747	PNL-CS-12LCW-PT	760221705	PNL-CS-24LCW-PT	760221788	PNL-CS-12SCW-PT
SM APC	760222596	PNL-CS-12LAW-PT	760222588	PNL-CS-24LAW-PT	760222604	PNL-CS-12SAW-PT
Without Pigtail						
OM4	760236500	PNL-CS-12LCX	760236503	PNL-CS-24LCX	760236506	PNL-CS-12SCX
OM5	760242110	PNL-CS-12LCV	760242111	PNL-CS-24LCV	-	-
SM UPC	760236501	PNL-CS-12LCW	760236504	PNL-CS-24LCW	760236507	PNL-CS-12SCW
SM APC	760236502	PNL-CS-12LAW	760236505	PNL-CS-24LAW	760236508	PNL-CS-12SAW
Blank Cassette						
Blank	760237458	PNL-CS-00000	SPlicing CASSETTE BLANK			

Fiber Panel Portfolios

APAC Local Splicing Solutions



1U 36/72F FIBER SPLICING SHELVE (SUPPORT 1000-TYPE ADAPTOR PLATE)

Material ID	Description			
760241725	1U Empty Shelf, support 3 1000-type adaptor plates			
760241378	48F Splice Tray Kit with SMOUV			
760198325	1000 TYPE to G2 type ADPT KIT			
EM2454-001	1000 TYPE ADAPTER PLATE ASSY BLANK			
Adaptor Plate	12 LC Duplex	6 LC Duplex	6 SC Duplex	12 SC Simplex
OM4 (AQUA)	EK5808-001	EK5806-001	760241027	-
OM5 (Lime Green)	760242759	760242760	-	-
SM UPC (Blue)	EK5809-001	EK5807-001	EM1828-001	760242756
SM APC (Green)	760241025	760241026	760241028	760242438
Adaptor Plate	2 ports	6 ports	8 ports	12 ports
MPO Aligned Key	760015412	760034280	760056077	760242757
MPO Key up- Key down	-	-	-	760242758



1U 12F/24F/48F/96F FIBER SPLICING SHELVE (INCLUDES ADAPTORS)

Material ID	Description
760245721	1U PANEL 12SC SIMP SM
760245722	1U PANEL 24SC SIMP SM
760249184	1U PANEL 48SC SIMP SM
760249187	1U PANEL 12SC SIMP MM
760249188	1U PANEL 24SC SIMP MM
760249186	1U PANEL 48SC SIMP MM
760241650	1U PANEL 12LC DUPL SM
760241651	1U PANEL 24LC DUPL SM
760249183	1U PANEL 48LC DUPL SM
760241652	1U PANEL 12LC DUPL MM
760241653	1U PANEL 24LC DUPL MM
760249185	1U PANEL 48LC DUPL MM

Fiber Panel Portfolios

FMS All-In-One Splicing Panel



Material ID	Product Number	Description
760254122	FMS-K1BI-S1A1-12-SP	FMS Panel, 1U, 19 in, black, Includes 6 x SC SM Duplex Adaptors (12F), 12 x SM SC Pigtailes. 12 x Splice protectors. Splice tray and cable glands
760254435	FMS-K2BI-S1A1-24-SP	FMS Panel, 1U, 19 in, black, Includes 12 x SC SM Duplex Adaptors (24F), 24 x SM SC Pigtailes. 24 x Splice protectors. Splice tray and cable glands
760254436	FMS-K1BI-L1A1-12-SP	FMS Panel, 1U, 19 in, black, Includes 6 x LC SM Duplex Adaptors (12F), 12 x SM LC Pigtailes. 12 x Splice protectors. Splice tray and cable glands
760254437	FMS-K2BI-L1A1-24-SP	FMS Panel, 1U, 19 in, black, Includes 12 x LC SM Duplex Adaptors (24F), 24 x SM LC Pigtailes. 24 x Splice protectors. Splice trays (2) and cable glands
760254438	FMS-K2BI-L1A1-48-SP	FMS Panel, 1U, 19 in, black, Includes 24 x LC SM Duplex Adaptors (48F), 48 x SM LC Pigtailes. 48 x Splice protectors. Splice trays (2) and cable glands
760254439	FMS-K1BI-SOM4-12-SP	FMS Panel, 1U, 19 in, black, Includes 6 x SC OM4 Duplex Adaptors (12F), 12 x OM4 SC Pigtailes. 12 x Splice protectors. Splice tray and cable glands
760254440	FMS-K2BI-SOM4-24-SP	FMS Panel, 1U, 19 in, black, Includes 12 x SC OM4 Duplex Adaptors (24F), 24 x OM4 SC Pigtailes. 24 x Splice protectors. Splice tray and cable glands
760254441	FMS-K1BI-LOM4-12-SP	FMS Panel, 1U, 19 in, black, Includes 6 x LC OM4 Duplex Adaptors (12F), 12 x OM4 LC Pigtailes. 12 x Splice protectors. Splice tray and cable glands
760254442	FMS-K2BI-LOM4-24-SP	FMS Panel, 1U, 19 in, black, Includes 12 x LC OM4 Duplex Adaptors (24F), 24 x OM4 LC Pigtailes. 24 x Splice protectors. Splice trays (2) and cable glands
760254443	FMS-K2BI-LOM4-48-SP	FMS Panel, 1U, 19 in, black, Includes 24 x LC OM4 Duplex Adaptors (48F), 48 x OM4 LC Pigtailes 48 x Splice protectors. Splice trays (2) and cable glands

Fiber Connectors and Adapters



QWIK II CONNECTORS KITS

Material ID	Product Number	Connector	Fiber	Cable	Housing color	Package
760117887	MFC-LCF-09-5X	LC	OM3/4/5	0.25/0.9 mm	Aqua	Single
760242343	MFC-LCF-UNV-5X*	LC	OM3/4/5	0.25/0.9/2.0/3.0 mm	Aqua	Single
760117895	SFC-LCF-09-8X	LC-UPC	OS2	0.25/0.9 mm	Blue	Single
760242344	SFC-LCF-UNV-8X*	LC-UPC	OS2	0.25/0.9/2.0/3.0 mm	Blue	Single
760242345	SFC-LCAF-UNV-8X*	LC-APC	OS2	0.25/0.9/2.0/3.0 mm	Green	Single
760184697	SFC-LCF-09-8A-25-PACK	LC-APC	OS2	0.25/0.9 mm	Green	25/pack
760117945	MFC-SCF-09-5X	SC	OM3/4/5	0.25/0.9 mm	Aqua	Single
760242346	MFC-SCF-UNV-5X*	SC	OM3/4/5	0.25/0.9/2.0/3.0 mm	Aqua	Single
760117952	SFC-SCF-09-8X	SC-UPC	OS2	0.25/0.9 mm	Blue	Single
760242347	SFC-SCF-UNV-8X*	SC-UPC	OS2	0.25/0.9/2.0/3.0 mm	Blue	Single
760242348	SFC-SCAF-UNV-8X*	SC-APC	OS2	0.25/0.9/2.0/3.0 mm	Green	Single
760184689	SFC-SCF-09-8A-25-PACK	SC-APC	OS2	0.25/0.9 mm	Green	25/pack
760253591	MFC-STF-UNV-5X	ST	OM3/4/5	0.25/0.9 mm	Aqua	Single
760253592	SFC-STF-UNV-8X	ST-UPC	OS2	0.25/0.9 mm	Blue	Single
760253593	MFC-STF-UNV-6X	ST	OS1	0.25/0.9 mm	Beige	Single

Material ID	Description
760242377	Basic, Toolkit, Qwik II Connector Termination
760248225	Premium Termination Toolkit for Field Installable Qwik II Connectors
760053207	Cleaning Consumables Kit, Fiber Optic


APAC LOCAL LC/SC ADAPTERS

Material ID	Description	Interface	Type
EH1457-002	LC Duplex Adapter, Flanged, Aqua	LC	MM
EH1458-002	LC Duplex Adapter, Flangeless, Aqua	LC	MM
CZ9340-000	LC/UPC Duplex Adapter, Flanged, Blue	LC	SM
CZ7270-000	LC/UPC Duplex Adapter, Flangeless, Blue	LC	SM
CZ7271-000	LC/APC Duplex Adapter, Flanged, Green	LC/APC	SM
CZ9341-000	LC/APC Duplex Adapter, Flangeless, Green	LC/APC	SM
2-5502776-6	SC/UPC Duplex Adapter, Flanged, Aqua	SC	MM
CZ9337-000	SC/UPC Duplex Adapter, Flanged, Blue	SC	SM
CZ9339-000	SC/APC Duplex Adapter, Flanged, Green	SC/APC	SM
CZ9338-000	SC/APC Duplex Adapter, Flangeless, Green	SC/APC	SM
CZ7267-000	SC/UPC Simplex Adapter, Flanged, Blue	SC	SM
CZ7266-000	SC/UPC Simplex Adapter, Flangeless, Blue	SC	SM
CZ9336-000	SC/APC Simplex Adapter, Flanged, Green	SC/APC	SM
CZ7268-000	SC/APC Simplex Adapter, Flangeless, Green	SC/APC	SM

QWIK-Fuse Connector Kits

The CommScope QWIK-Fuse connector utilizes fusion-splicing connectivity to ensure best-in-class insertion & return loss performance. They're designed to be compatible with the fusion splicer already in your toolbox using the included ferrule holder, though CommScope does offer a competitively priced splicer specifically for connector installation as well. Unlike many fusion-splice connectors, with the QWIK-Fuse, the splice is entirely contained within a standard connector footprint. Available in LC and SC connector styles, choose QWIK-Fuse when market-leading insertion & return loss performance is a priority.

Fiber	SMF (OS2) MMF (OM3/4/5)
Cable diameter	250 µm, 900 µm, 1.6 mm, 2.0 mm, 3.0 mm
Polish	APC, UPC
Insertion loss	SMF: 0.15 dB (typical), 0.3 dB (max) MMF: 0.10 dB (typical), 0.25 dB (max)
Return loss	SMF: ≥65 dB (APC), ≥55 dB (UPC) MMF: ≥30 dB (PC)
Operating temperature	-40°C to 75°C
Housing color	SMF: Green (APC), Blue (UPC) MMF: Aqua
Standard compliance	SM: GR-326-CORE, TIA 568-3. D, and IEC 61753-1 MM: TIA 568-3. D and IEC 61753-1



QWIK-FUSE CONNECTOR KITS

Material ID	Description	Connector	Fiber	Cable	Housing color	Package
760242874	MFC-LCF-09-5Y-12-PACK	LC	OM3/4/5	0.25/0.9 mm	Aqua	12/pack
760243371	MFC-LCF-20-5Y-12-PACK	LC	OM3/4/5	1.6/2.0 mm	Aqua	12/pack
760243372	SFC-LCF-09-8Y-12-PACK	LC-UPC	OS2	0.25/0.9 mm	Blue	12/pack
760243388	SFC-LCF-20-8Y-12-PACK	LC-UPC	OS2	1.6/2.0 mm	Blue	12/pack
760243389	SFC-LCAF-09-8Y-12-PACK	LC-APC	OS2	0.25/0.9 mm	Green	12/pack
760243390	SFC-LCAF-20-8Y-12-PACK	LC-APC	OS2	1.6/2.0 mm	Green	12/pack
760243391	MFC-SCF-09-5Y-12-PACK	SC	OM3/4/5	0.25/0.9 mm	Aqua	12/pack
760243392	MFC-SCF-20-5Y-12-PACK	SC	OM3/4/5	1.6/2.0 mm	Aqua	12/pack
760243393	MFC-SCF-30-5Y-12-PACK	SC	OM3/4/5	3.0 mm	Aqua	12/pack
760243394	SFC-SCF-09-8Y-12-PACK	SC-UPC	OS2	0.25/0.9 mm	Blue	12/pack
760243395	SFC-SCF-20-8Y-12-PACK	SC-UPC	OS2	1.6/2.0 mm	Blue	12/pack
760243396	SFC-SCF-30-8Y-12-PACK	SC-UPC	OS2	3.0 mm	Blue	12/pack
760243397	SFC-SCAF-09-8Y-12-PACK	SC-APC	OS2	0.25/0.9 mm	Green	12/pack
760243398	SFC-SCAF-20-8Y-12-PACK	SC-APC	OS2	1.6/2.0 mm	Green	12/pack
760243399	SFC-SCAF-30-8Y-12-PACK	SC-APC	OS2	3.0 mm	Green	12/pack

QWIK-Fuse Tool Kits and Accessories

CommScope Qwik-Fuse connector tool kits are designed to facilitate fast and reliable connector terminations. The Qwik-Fuse Termination Tool Kit includes all necessary tools and supplies for cable preparation and termination—providing great convenience to installers and contractors. In addition to all components in the tool kit, the Qwik-Fuse Installer Tool Kit includes a purpose-built splicer (Installer) and fiber holders, which significantly simplify and speed up the splice-on termination process. Fiber holders to terminate Qwik-Fuse connectors using other industry-leading splicers are also available from CommScope.

Qwik-Fuse single fiber connector tool kits

Component	Qwik-Fuse Termination Kit (760243402)	Qwik-Fuse Installer Kit (760243403)
Case	√	√
Qwik-Fuse Installer		√
Installer power supply		√
Installer spare electrodes		√
Fiber holder, tight buffer		√
Fiber holder, loose buffer		√
Cord prep tool	√	√
High-precision cleaver	√	√
Fiber stripper, 3-hole	√	√
Cutter, Kevlar	√	√
Marker, Sharpie	√	√
Fiber prep fluid	√	√
Fiber wipes	√	√
Termination instruction	√	√




QWIK-FUSE TOOL KITS AND ACCESSORIES

Material ID	Description
760243402	Qwik-Fuse Termination Tool Kit, LC, SC (for splice-on connector termination)
760243403	Qwik-Fuse Installer Tool Kit, LC, SC, with Qwik-Fuse Installer and termination tools
760244684	Qwik-Fuse cord tool, 1.6, 2.0, 3.0 mm
760243576	Qwik-Fuse Installer
760243617	Qwik-Fuse fiber holder, tight buffer and cordage (for use with Qwik-Fuse Installer and many AFL and Sumitomo splicers)
760244521	Qwik-Fuse fiber holder, loose buffer and 250µm fiber (for use with Qwik-Fuse Installer and many AFL and Sumitomo splicers)
760244706	Qwik-Fuse fiber holder, Fitel, set
760245135	Qwik-Fuse connector duplex clip, LC, 10 per pack
760245136	Qwik-Fuse connector duplex clip, SC, 10 per pack
760245969	Qwik-Fuse metal ferrule holder

QWIK-Fuse MPO Connector Kits

The CommScope QWIK-Fuse MPO connector utilizes mass-fusion-splicing connectivity to facilitate rapid repairs, restorations, and upgrades to multi-fiber cable assemblies. They offer a reliable alternative when factory-terminated MPO solutions cannot be used, such as when high-fiber count cables are being fed through tight conduits or when slack storage of the multi-fiber breakout cannot be accommodated. The ferrule holder that is required for terminations is included with the QWIK-Fuse MPO termination kit and is also available separately.



Fiber	SMF (OS2) MMF (OM3/4/5)
Fiber counts	8, 12
Cable construction/diameter	3.0 mm round, ribbon–no jacket, ribbon with jacket
Polish	APC, PC
Insertion loss	SMF: ≤ 0.75 dB (Standard loss) ≤ 0.35 dB (Low loss) MMF: ≤ 0.35 dB
Return loss	SMF: ≥ 60 dB (APC) MMF: ≥ 20 dB (PC)
Operating temperature	-40°C to 75°C
Housing color	SMF: Yellow (Low loss) Green (Standard loss) MMF: Aqua (OM3/4/5)
Standard compliance	TIA 568-3. D

QWIK-FUSE MPO CONNECTOR KITS

Material ID	Description	Connector	Fiber	Cable	Housing color	Performance	Package
760251300	MFC-12MX-5SP-30-AQ, QWIK MPO, PINNED	MPO-PC Pinned	OM3/4/5	12f round, 3.0 mm	Aqua	Standard Loss	Single
760251299	MFC-12MP-5SP-30-AQ, QWIK MPO, UNPINNED	MPO-PC Unpinned	OM3/4/5	12f round, 3.0 mm	Aqua	Standard Loss	Single
760251294	MFC-12MX-5SP-RN-AQ, QWIK MPO, PINNED	MPO-PC Pinned	OM3/4/5	12 f ribbon, no jacket	Aqua	Standard Loss	Single
760251293	MFC-12MP-5SP-RN-AQ, QWIK MPO, UNPINNED	MPO-PC Unpinned	OM3/4/5	12 f ribbon, no jacket	Aqua	Standard Loss	Single
760251292	MFC-12MX-5SP-RC-AQ, QWIK MPO, PINNED	MPO-PC Pinned	OM3/4/5	12 f ribbon, with jacket	Aqua	Standard Loss	Single
760251291	MFC-12MP-5SP-RC-AQ, QWIK MPO, UNPINNED	MPO-PC Unpinned	OM3/4/5	12 f ribbon, with jacket	Aqua	Standard Loss	Single
760248909	MFC-8MX-5SP-30-AQ, MPO-PC, PINNED	MPO-PC Pinned	OM3/4/5	8f round, 3.0 mm	Aqua	Standard Loss	Single
760248910	MFC-8MP-5SP-30-AQ, MPO-PC, UNPINNED	MPO-PC Unpinned	OM3/4/5	8f round, 3.0 mm	Aqua	Standard Loss	Single
760248915	MFC-8MX-5SP-RN-AQ, MPO-PC, PINNED	MPO-PC Pinned	OM3/4/5	8f ribbon, no jacket	Aqua	Standard Loss	Single
760248916	MFC-8MP-5SP-RN-AQ, MPO-PC, UNPINNED	MPO-PC Unpinned	OM3/4/5	8f ribbon, no jacket	Aqua	Standard Loss	Single

QWIK-Fuse MPO Connector Kits

QWIK-FUSE MPO CONNECTOR KITS (CONTINUED)

Material ID	Description	Connector	Fiber	Cable	Housing color	Performance	Package
760248917	MFC-8MX-5SP-RC-AQ, MPO-PC, PINNED	MPO-PC Pinned	OM3/4/5	8f ribbon, with jacket	Aqua	Standard Loss	Single
760248918	MFC-8MP-5SP-RC-AQ, MPO-PC, UNPINNED	MPO-PC Unpinned	OM3/4/5	8f ribbon, with jacket	Aqua	Standard Loss	Single
760251302	SFC-12MX-8SP-30-GR, QWIK MPO/APC, PINNED	MPO-APC Pinned	OS2	12f round, 3.0 mm	Green	Standard Loss	Single
760251301	SFC-12MP-8SP-30-GR, QWIK MPO/APC, UNPINNED	MPO-APC Unpinned	OS2	12f round, 3.0 mm	Green	Standard Loss	Single
760251298	SFC-12MX-8SP-RN-GR, QWIK MPO/APC, PINNED	MPO-APC Pinned	OS2	12 f ribbon, no jacket	Green	Standard Loss	Single
760251297	SFC-12MP-8SP-RN-GR, QWIK MPO/APC, UNPINNED	MPO-APC Unpinned	OS2	12 f ribbon, no jacket	Green	Standard Loss	Single
760251296	SFC-12MX-8SP-RC-GR, QWIK MPO/APC, PINNED	MPO-APC Pinned	OS2	12 f ribbon, with jacket	Green	Standard Loss	Single
760251295	SFC-12MP-8SP-RC-GR, QWIK MPO/APC, UNPINNED	MPO-APC Unpinned	OS2	12 f ribbon, with jacket	Green	Standard Loss	Single
760249953	SFC-12MP-8LL-30-YL, MPO-APC, UNPINNED	MPO-APC Unpinned	OS2	12f round, 3.0 mm	Yellow	Low Loss	Single
760249954	SFC-12MP-8LL-RN-YL, MPO-APC, UNPINNED	MPO-APC Unpinned	OS2	12 f ribbon, no jacket	Yellow	Low Loss	Single
760249955	SFC-12MP-8LL-RC-YL, MPO-APC, UNPINNED	MPO-APC Unpinned	OS2	12 f ribbon, with jacket	Yellow	Low Loss	Single
760249956	SFC-12MX-8LL-30-YL, MPO-APC, PINNED	MPO-APC Pinned	OS2	12f round, 3.0 mm	Yellow	Low Loss	Single
760249957	SFC-12MX-8LL-RN-YL, MPO-APC, PINNED	MPO-APC Pinned	OS2	12 f ribbon, no jacket	Yellow	Low Loss	Single
760249958	SFC-12MX-8LL-RC-YL, MPO-APC, PINNED	MPO-APC Pinned	OS2	12 f ribbon, with jacket	Yellow	Low Loss	Single

QWIK-FUSE MPO TOOL KITS AND ACCESSORIES

Material ID	Description
760188698	Qwik MPO connector termination tool kit (Includes: Assembly platform, ferrule holder, jacket stripper/splitting tool, ribbonizing tool, ribbonizing glue, magnifier, marker, instructions, and soft case)

Method A MPO Trunk and Patch Cords



METHOD A MPO-12 TRUNK CABLES

1 A	2 J	3 X	4 M	5 X	6 M	7 X	8 A	9 K	10 -	11 M	12 A	13 F	14-16 010
Construction type A Method A	Family G Trunk, Plenum J Trunk, LSZH/ Riser	Fiber type G Singlemode (A2) X OM4 multimode	Termination end A MP MPO (female) MX MPO (male)	Termination end B MP MPO (female) MX MPO (male)	Construction A 12 Fiber PmP	Fiber count D 12-fiber F 24-fiber H 48-fiber K 72-fiber L 96-fiber M 144-fiber	Color M Aqua J Yellow	Options A No gland B With gland C With pulling eye	Unit of measure F Feet M Meter	Length 010-999 Feet 003-305 Meter			
- Male to female will be configured as trunk extensions						- OM4 standard is aqua - Singlemode standard is yellow							

METHOD A MPO-24 TRUNK CABLES

1 A	2 G	3 V	4 2	5 X	6 2	7 X	8 B	9 M	10 -	11 M	12 C	13 F	14-16 010
Construction type A Method A	Family G Trunk, Plenum J Trunk, LSZH/ Riser	Fiber type X OM4 multimode	Termination end A 2P MPO (female) 2X MPO (male)	Termination end B 2P MPO (female) 2X MPO (male)	Construction B 24-fiber PmP	Fiber count F 24-fiber H 48-fiber K 72-fiber L 96-fiber M 144-fiber	Color M Aqua	Options A No gland B With gland C With pulling eye	Unit of measure F Feet M Meter	Length 010-999 Feet 003-305 Meter			
- Male to female will be configured as trunk extensions						- OM4 standard is aqua							


METHOD A MPO-12 PATCH CORDS

1 A	2 Q	3 G	4 M	5 X	6 M	7 X	8 G	9 D	10 -	11 J	12 A	13 F	14-16 010
Construction type A Method A	Cable family Q Plenum array R LSZH array	Fiber type G Singlemode (A2) X OM4 multimode	Connector 1 MP 12f MPO (female) MX 12f MPO (male)	Connector 2 MP 12f MPO (female) MX 12f MPO (male) UC Unconnected	Cordage size G 12-fiber PmP Array Cord	Fiber count D 12-fiber	Color M Aqua J Yellow	Breakout length A No gland	UOM F Feet M Meter	Length 010-999 ft 003-305 m			

METHOD A MPO-24 PATCH CORDS

1 A	2 Q	3 X	4 2	5 X	6 2	7 X	8 H	9 F	10 -	11 M	12 A	13 F	14-16 010
Construction type A Method A	Cable family Q Plenum array R LSZH array	Fiber type X OM4 multimode	Connector 1 2P 24f MPO (female) 2X 24f MPO (male)	Connector 2 2P 24f MPO (female) 2X 24f MPO (male) UC Unconnected	Cordage size H 24-fiber PmP Array Cord	Fiber count F 24-fiber	Color M Aqua	Breakout length A No gland	UOM F Feet M Meter	Length 010-999 ft 003-305 m			

Fiber Patch Cords




LL FIBER OPTIC LC PATCH CORDS

- Duplex zipcord construction provides better mechanical performance with less risk of damage from crimping
- Rugged 1.6 mm cordage for durable and easily handled connections
- Outer jacket colored for easy identification

1 F	2 D	3 X	4 L	5 C	6 L	7 C	8 4	9 2	10 -	11 M	12 X	13 F	14-16 010
Prefix FD Jumper-Plenum FF Jumper-LSZH/ Riser	Fiber Type X OM4 W Single-mode (A1)	Connector 1 LC LC Standard SC SC Standard LA LC Angled SA SC Angled	Connector 2 LC LC Standard SC SC Standard LA LC Angled SA SC Angled	Cordage Size 2 1.6mm Simplex 4 1.6mm Zipcord	Fiber Count 1 1 Fiber 2 2 Fiber	Jacket Color M Aqua J Yellow	Breakout Length X No Breakout	UOM F Feet M Meter	Breakout 2-200 1-061	Length Feet Meters			

· OM4 standard is aqua

· Singlemode standard is yellow



ULL FIBER OPTIC LC PATCH CORDS

- Duplex zipcord construction provides better mechanical performance with less risk of damage from crimping
- Rugged 1.6 mm cordage for durable and easily handled connections
- Outer jacket colored for easy identification

1 U	2 D	3 X	4 L	5 C	6 L	7 C	8 4	9 2	10 -	11 M	12 X	13 F	14-16 010
Construction type U Ultra-low loss	Cable family D Plenum F LSZH/Riser	Fiber type G Singlemode (A2) X OM4 V OM5	Connector 1 LC Standard	Connector 2 LC LC Standard UC Unconnectorized	Cordage size 2 1.6mm simplex 4 1.6mm zipcord	Fiber count 1 1-fiber 2 2-fiber	Color M Aqua N Lime green J Yellow	Breakout length X No breakout	UOM F Feet M Meter	Length 2-200 1-061	Feet Meters		

· OM4 standard is aqua

· OM5 standard is lime green

· Singlemode standard is yellow

· Other lengths available please contact CommScope

Fiber Pigtails



900µm PIGTAIL (SINGLE FIBER)

Fiber	Buffer	Performance	Fiber Count	LC	SC
SM A1 UPC	Tight	LL	1	FAWLCUC01-JXF003	FAWSCUC01-JXF003
SM A1 APC	Tight	LL	1	FAWLAUC01-JXF003	FAWSAUC01-JXF003
OM4	Tight	LL	1	FAXLCUC01-MXF003	FAXSCUC01-MXF003
OM4	Tight	ULL	1	UAXLCUC01-MXF003	UAXSCUC01-MXF003
OM5	Tight	ULL	1	UAVLCUC01-NXF003	-
SM A1 UPC	Tight	ULL	1	UAWLCUC01-JXF003	-

900µm PIGTAIL KIT (12 COLOR)

Fiber	Buffer	Performance	Fiber Count	LC	SC
SM A1	Tight	LL	12	FAWLCUC0C-XXF003	FAWSCUC0C-XXF003
SM A1/APC	Tight	LL	12	FAWLAUC0C-XXF003	FAWSAUC0C-XXF003
OM4	Tight	LL	12	FAXLCUC0C-XXF003	FAXSCUC0C-XXF003
OM4	Tight	ULL	12	UAXLCUC0C-XXF003	-
OM5	Tight	ULL	12	UAVLCUC0C-XXF003	-
SM A1 UPC	Tight	ULL	12	UAWLCUC0C-XXF003	-

900µm PIGTAIL (SINGLE FIBER) WITH KEVLAR

Fiber	Buffer	Performance	Fiber Count	LC	SC
SM A1 UPC	Semi-Tight	LL	1	FBWLCUC11-JXF003	FBWSCUC11-JXF003
SM A1 APC	Semi-Tight	LL	1	FBWLAUC11-JXF003	FBWSAUC11-JXF003
OM4	Semi-Tight	LL	1	FBXLCUC11-MXF003	FBXSCUC11-MXF003
OM4	Semi-Tight	ULL	1	UBXLCUC11-MXF003	UBXSCUC11-MXF003
OM5	Semi-Tight	ULL	1	UBVLCUC11-NXF003	-
SM A1 UPC	Semi-Tight	ULL	1	UBWLCUC11-JXF003	-

APAC Local Fiber Patch Cords and Pigtails



PATCH CORDS							
Fiber	Jacket	Cable OD	Performance	Fiber Count	LC-LC Duplex	LC-SC Duplex	SC-SC Duplex
OM4	LSZH&OFNR	LL	1.8mm	2	Y-2105061-X	Y-2105067-X	Y-2105093-X
OM3	LSZH&OFNR	LL	1.8mm	2	Y-2105027-X	-	-
SM A2	LSZH&OFNR	LL	1.8mm	2	Y-2105028-X	Y-2105032-X	Y-2105092-X
OM4	LSZH&OFNR	LL+	1.8mm	2	Y-2160046-X	-	-
OM3	LSZH&OFNR	LL+	1.8mm	2	Y-1920743-X	Y-2055109-X	Y-2055108-X




900µm PIGTAILS					
Fiber	Buffer	Performance	Fiber Count	LC	SC
SM G.657A1	Tight	LL	1	2105081-X	2105082-X
OM3	Tight	LL	1	2105083-X	2105085-X
OM4	Tight	LL	1	2105084-X	2105086-X

APAC Local Fiber Patch Cords and Pigtails

CAF COMMSCOPE ARMORED FIBER PATCHCORD

- Optical performance
 - Multimode Max IL: 0.30 dB
 - Singlemode Max IL: 0.25 dB
- 3.0mm OD Armored cable
 - Outer Jacket: $3.0 \pm 0.1\text{mm}$
 - Jacket Material: LSZH
 - Armor Type: Stainless Steel 204
- 1F cable Tensile Strength: $\leq 200\text{N}$ (Short Term), $\leq 100\text{N}$ (Long Term)
- 2F cable Tensile Strength: $\leq 400\text{N}$ (Short Term), $\leq 200\text{N}$ (Long Term)
- Crush Resistance: $\leq 4000\text{N}/100\text{mm}$ (Short Term), $\leq 2000\text{N}$ (Long Term)



Fiber Type	Jacket	OD	Connector	1F	2F
G.657.A2	LSZH	3.0mm	LC/UPC to LC/UPC	CAF-LCLC-LS0MxxxM	CAF-LCLC-LS0NxxxM
G.657.A2	LSZH	3.0mm	LC/APC to LC/APC	CAF-7C7C-LS0MxxxM	CAF-7C7C-LS0NxxxM
G.657.A2	LSZH	3.0mm	SC/UPC to SC/UPC	CAF-SCSC-LS0MxxxM	CAF-SCSC-LS0NxxxM
G.657.A2	LSZH	3.0mm	SC/APC to SC/APC	CAF-6C6C-LS0MxxxM	CAF-6C6C-LS0NxxxM
OM4	LSZH	3.0mm	LC/UPC to LC/UPC		CAF-LCLC-L40NxxxM
OM4	LSZH	3.0mm	SC/UPC to SC/UPC		CAF-SCSC-L40NxxxM

Rack and Cabinet



COMMSCOPE OPEN RACK - ASEAN			
MATERIAL ID	PRODUCT NUMBER	DESCRIPTION	HEIGHT
760082495	RK6-45A	Equipment Rack, 2-Post, 6 in (152 mm) Channel x 7 ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black	45U

COMMSCOPE WALL MOUNT RACK				
MATERIAL ID	DESCRIPTION	HEIGHT	WIDTH X DEPTH	DOOR
1427517-1	CommScope Wall Rack 600X500, 6U, Acrylic Door	6U	600 x 500	Acrylic
1427517-2	CommScope Wall Rack 600X500, 6U, Curve Perforate Door	6U	600 x 500	Curve Perforate
1427520-1	CommScope Wall Rack 600X650, 6U, Acrylic Door	6U	600 x 650	Acrylic
1427520-2	CommScope Wall Rack 600X650, 6U, Curve Perforate Door	6U	600 x 650	Curve Perforate
1427518-1	CommScope Wall Rack 600X500, 9U, Acrylic Door	9U	600 x 500	Acrylic
1427518-2	CommScope Wall Rack 600X500, 9U, Curve Perforate Door	9U	600 x 500	Curve Perforate
1427521-1	CommScope Wall Rack 600X650, 9U, Acrylic Door	9U	600 x 650	Acrylic
1427521-2	CommScope Wall Rack 600X650, 9U, Curve Perforate Door	9U	600 x 650	Curve Perforate
1427519-2	CommScope Wall Rack 600X500, 12U, Curve Perforate Door	12U	600 x 500	Curve Perforate
1427522-1	CommScope Wall Rack 600X650, 12U, Acrylic Door	12U	600 x 650	Acrylic
1427522-2	CommScope Wall Rack 600X650, 12U, Curve Perforate Door	12U	600 x 650	Curve Perforate

Rack and Cabinet

COMMSCOPE RACK ACCESSORIES - SHELVES		
MATERIAL ID	DESCRIPTION	DEPTH
1427510-1	CommScope Fix shelf, for 600 Series, 450 mm	450
1427510-2	CommScope Fix shelf heavy duty, for 600 Series, 450 mm	450
1427510-3	CommScope Fix shelf, for 800 Series, 600 mm	600
1427510-4	CommScope Fix shelf heavy duty, for 800 Series, 600 mm	600
1427510-5	CommScope Fix shelf, for 1100 Series, 800 mm	800
1427510-6	CommScope Fix shelf heavy duty, for 1100 Series, 800 mm	800

COMMSCOPE RACK ACCESSORIES - FANS		
MATERIAL ID	DESCRIPTION	SIZE
1427508-1	CommScope Ventilating fan set 2x4"	2x4
1427508-2	CommScope Ventilating fan set 3x4"	3x4

COMMSCOPE RACK ACCESSORIES - AC POWER DISTRIBUTION UNITS		
MATERIAL ID	DESCRIPTION	OUTLET
1427507-1	CommScope AC Power Distribution Unit, 6 outlet (Std)	6
1427507-2	CommScope AC Power Distribution Unit, 12 outlet(Std)	12
1-1427507-1	CommScope AC Power Distribution Unit, 6 outlet power plug	6
1-1427507-2	CommScope AC Power Distribution Unit, 12 outlet power plug	12

CommScope pushes the boundaries of communications technology with game-changing ideas and ground-breaking discoveries that spark profound human achievement.

We collaborate with our customers and partners to design, create and build the world's most advanced networks. It is our passion and commitment to identify the next opportunity and realize a better tomorrow. Discover more at commscope.com

COMMSCOPE®

commscope.com

Visit our website or contact your local CommScope representative for more information.

© 2023 CommScope, Inc. All rights reserved.

CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see <https://www.commscope.com/trademarks>. All product names, trademarks and registered trademarks are property of their respective owners.