



Propel ULL Singlemode MPO-12 Distribution Module, 12 duplex LC to 2X12f MPO/APC pinned, Method A Pairs Flipped

- Ultra-low loss (ULL) with Method A polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 6 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Breakout module
Product Brand	Propel
Product Series	PPL

General Specifications

Functionality	Breakout
Color, front	Blue
Color, rear	Black
Interface, front	LC/UPC
Interface Feature, front	Internal shutters
Interface, rear	MPO
Interface Feature, rear	Internal shutters Key up/down MPO Pinned Standard
Polarity	Method A Pairs, flipped
Total Fibers, quantity	24
Total Ports, quantity, front	12
Total Ports, quantity, rear	2

Dimensions

Height	11 mm 0.433 in
Width	196 mm 7.717 in
Depth	170 mm 6.693 in

Optical Specifications

760256135 | PPL-DM-12AP-24LC-SM-AF

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.6 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	CE CSA UL UL 62368

Packaging and Weights

Packaging quantity	1
---------------------------	---